



EMI & EMC Solutions > IEC Inlets > Inlet Filters > FN9244 / FN9244E IEC Inlet Filters – Superior EMC/RFI Performance with Optional Earth Line Choke



Filtering Requirements: **Filtered**  
Current Rating (Max): **10 A**  
Output Termination Type: **FASTON**  
Pollution Degree: **PD2**  
IP Rating: **IP40**

[All FN9244 / FN9244E IEC Inlet Filters – Superior EMC/RFI Performance with Optional Earth Line Choke \(177\)](#)

Features

Product Type Features

|                         |                      |
|-------------------------|----------------------|
| Filter Type             | IEC Inlet Filter     |
| Level Of Filtering      | Inductor & Capacitor |
| Filtering Requirements  | Filtered             |
| Output Termination Type | FASTON               |
| Ground Choke Option     | Yes                  |

Electrical Characteristics

|                                      |              |
|--------------------------------------|--------------|
| Inductance L1                        | 1.02 $\mu$ H |
| Capacitance Cx1                      | .1           |
| Overvoltage Category                 | II           |
| Current Rating (Max)                 | 10 A         |
| Leakage Current (Max) (120VAC, 60Hz) | 0 $\mu$ A    |
| Leakage Current (Max) (250VAC, 50Hz) | 0 $\mu$ A    |



Body Features

|                |               |
|----------------|---------------|
| Product Weight | 38 g[1.34 oz] |
|----------------|---------------|

Dimensions

|                |                   |
|----------------|-------------------|
| Product Width  | 22.4 mm[.88 in]   |
| Product Length | 29.9 mm[1.17 in]  |
| Product Height | 43.95 mm[1.73 in] |

Operation/Application

|                |                    |
|----------------|--------------------|
| Cooling Method | Natural Convection |
|----------------|--------------------|

Industry Standards

|                        |                                            |
|------------------------|--------------------------------------------|
| Certified To           | CSA 22.2 No. 8 1986, IEC/EN 60939, UL 1283 |
| Pollution Degree       | PD2                                        |
| IP Rating              | IP40                                       |
| UL Flammability Rating | UL 94V-2                                   |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Not Yet Reviewed                                                                                                                |
| China RoHS 2 Directive MIIT Order No 32, 2016 | 未针对中国 RoHS 符合性进行审核 Not reviewed for China RoHS compliance                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2025 (250)<br>Candidate List Declared Against: JUNE 2025 (250)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Yet Reviewed for halogen content                                                                                            |
| Solder Process Capability                     | Not reviewed for solder process capability                                                                                      |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for



substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



## Also in the Series | [Schaffner FN9244](#)



## Customers Also Bought



## Documents

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_804080-SF\\_F.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_804080-SF\\_F.3d\\_stp.zip](#)

English



3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_804080-SF\_F.3d\_igs.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

IEC Inlet Filters FN9244

English

Agency Approvals

CB SE-93907

English