




EMI & EMC Solutions > EMC Filters > Power Line Filters > 3-Phase Filters > 3-Phase Filters, EMC/RFI Filter for RCD-Compatible Installations



Current Rating: **130 A**

Input Termination Type: **Terminal Block**

Output Termination Type: **Terminal Block**

Wiring Configuration: **Three Phase**

Operating Voltage: **520 VAC**

[All 3-Phase Filters, EMC/RFI Filter for RCD-Compatible Installations \(9\)](#)

## Features

### Product Type Features

Filtering Requirements	Unfiltered
Input Termination Type	Terminal Block
Output Termination Type	Terminal Block

### Configuration Features

Wiring Configuration	Three Phase
----------------------	-------------

### Electrical Characteristics

Leakage Current (Max) (250VAC, 50Hz)	14.2 mA
Overvoltage Category	II
Current Rating	130 A
Operating Voltage	520 VAC

### Body Features

Product Weight	4600 g[162.26 oz]
----------------	-------------------

### Mechanical Attachment



Product Mount Type	Chassis Mount
--------------------	---------------

**Dimensions**

Product Width	90 mm[3.54 in]
Product Length	240 mm[9.44 in]
Product Height	150 mm[5.9 in]

**Usage Conditions**

Operating Temperature Range	-25 – 100 °C[-13 – 212 °F]
-----------------------------	----------------------------

**Operation/Application**

Cooling Method	Natural Convection
----------------	--------------------

**Industry Standards**

IP Rating	IP20
UL Flammability Rating	UL 94V-0
Pollution Degree	PD2
Certified To	CSA 22.2 No. 8 1986, IEC/EN 60939, UL 1283

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for

substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



## Also in the Series | Schaffner FN3268



## Customers Also Bought



## Documents

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_810320-SF\\_E.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_810320-SF\\_E.2d\\_dxf.zip](#)

English



### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_810320-SF\\_E.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[3-Phase Filters FN3268](#)

English

---

### Agency Approvals

[UKCA\\_FN-3ph-60939-3](#)

English