5-2103177-1 ✔ ACTIVE

TE Internal #: 5-2103177-1

TE Internal Description: PLUG ASSY, KEY A, FA, HVA280-2PHI XE

View on TE.com >







Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.26% in 35331746655) Dodecamethylcyclohexasiloxane (D6) (.26% in 35331746655) Decamethylcyclopentasiloxane (D5) (.26% in 35331746655) **Article Safe Usage Statements:** Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts

TE Part # YHVA280-2PHX-HDR-A
HVA280 2P (2103124-1) HEADER, KEY A



TE Part # 1587828-3
INNER FERRULE, SIZE C, HVA280-2PI



TE Part # 2103181-3
CABLE SEAL RTNR, SIZE C, HVA280-2PI XE



TE Part # 1587826-2
CABLE SEAL, SIZE B, HVA280-2PI




TE Part # 2103414-1
SHIPPING CAP TYPE 1, PLUG, HVA280



TE Part # 2103181-1
CABLE SEAL RTNR, SIZE A, HVA280-2PI XE



TE Part # 2103124-1
HVA280 2P HEADER ASSY, KEY A



TE Part # 1587826-1
CABLE SEAL, SIZE A, HVA280-2PI



TE Part # 1587829-2
OUTER FERRULE, SIZE B, HVA280-2PI



TE Part # 1587828-2
INNER FERRULE, SIZE B, HVA280-2PI



TE Part # 1587829-3
OUTER FERRULE, SIZE C, HVA280-2PI



TE Part # 2103181-2
CABLE SEAL RTNR, SIZE B, HVA280-2PI XE

Customers Also Bought



TE Part #CP4901-000
ES2000-NO.1-C1-0-40MM-SH



TE Part #SP1-50
STRING POT 50.0 INCH RANGE




TE Part #063725P011
ES2000-NO.2-B9-0-50MM




TE Part #DT13-4P
HDR, 4P, GRY, RA, NI/CU



TE Part #33461
TERMINAL,SOLIS R 8 1/4




TE Part #173716-1
040 HDIO REC CONT



TE Part #1-776230-1
35POS,PIN DIA 1.3,HDR ASSY, 180DEG,COD 1



TE Part #1-2103124-1
HEADER ASSY, Ag SHIELD, KEY A, HVA280-2P



TE Part #2-2141598-2
TAB 2.8x0.8 CONTACT CF SRC Ag



TE Part #2103181-3
CABLE SEAL RTNR, SIZE C, HVA280-2PI XE

Documents

Product Drawings

PLUG ASSY, KEY A, FA, HVA280-2PHI XE

English

PLUG ASSY, KEY A, FA, HVA280-2PHI XE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-2103177-1_B_c-5-2103177-1-b.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-2103177-1_B_c-5-2103177-1-b.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-2103177-1_B_c-5-2103177-1-b.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English