


OMIH-SS-124LM,000 × OBSOLETE

TE Internal #: 8-1419121-8

TE Internal Description: OMIH-SS-124LM,000

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #170363-1
MINI UNIVERSAL M-N-L PIN LP



TE Part #172333-1
MINI UNIVERSAL M-N-L HOUSING




TE Part #826926-2
AMPMODU II PIN HEADER



TE Part #826936-3
3P AMPMODU II STIFT LEI



TE Part #7-1625984-8
HSA50 6K8 5%



TE Part #4-1879666-6
H8 392K 0.1% 15PPM



TE Part #9-2176311-7
RP 1E 0.1W 11K5 0.1% 25PPM 1K RL



TE Part #5555153-1
MJ,LPF,R/A,8P,PCBG,PSTP.15TTR



TE Part #1932000-1
VERTICAL DDR3 DIMM, 240 POSITION



TE Part #1625878-2
FRN25 5% 10R

Documents

Product Drawings

[OMIH-SS-124LM,000](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_8-1419121-8_C2.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_8-1419121-8_C2.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_8-1419121-8_C2.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[OMI OMIH Series Relay Data Sheet English](#)

English

Product Specifications

[OMIH-SS-124LM,000 300 Spec Sheet](#)

Japanese

Definitions General Purpose Relays

English