

IL13P-CN1-RVW-3100-200 ✓ ACTIVE

Schaffner | [Schaffner IL13P](#)

TE Internal #: 815918-SF

250 VAC, 10 A, 200 mm [7.87 in], IP20, UL 94V-2, 1 mm² Wire, Black,

Schaffner IL13P, IEC Power Cords

[View on TE.com >](#)



EMI & EMC Solutions > IEC Power Cords > IL13P



Operating Voltage (Max): **250 VAC**

Current Rating (Max): **10 A**

Product Length: **200 mm [7.87 in]**

IP Rating: **IP20**

UL Flammability Rating: **UL 94V-2**

[All IL13P \(78\)](#)

Features

Electrical Characteristics

Operating Voltage (Max)	250 VAC
Current Rating (Max)	10 A

Body Features

Cable Color	Black
-------------	-------

Dimensions

Product Length	200 mm[7.87 in]
Wire Size	1 mm ²

Usage Conditions

Cable Type	Power Cable
------------	-------------

Industry Standards

IP Rating	IP20
UL Flammability Rating	UL 94V-2

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------




EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Also in the Series | Schaffner IL13P



IL13P-CN1-RVV-3100-200

250 VAC, 10 A, 200 mm [7.87 in], IP20, UL 94V-2, 1 mm² Wire, Black, Schaffner IL13P,
IEC Power Cords



Documents

[Datasheets & Catalog Pages](#)

[Power Cords with Locking System IL 13, 13 P, 19](#)

English