




EMI & EMC Solutions > IEC Inlets > Inlet Filters > FN9290 Power Entry Module with EMC Filter – Ultra-Compact Dual-Stage Filtering Solution



Filtering Requirements: **Filtered**

Current Rating (Max): **10 A**

Output Termination Type: **Terminal Block**

Pollution Degree: **PD2**

IP Rating: **IP40**

[All FN9290 Power Entry Module with EMC Filter – Ultra-Compact Dual-Stage Filtering Solution \(51\)](#)

Features

Product Type Features

|                         |                      |
|-------------------------|----------------------|
| Level Of Filtering      | Inductor & Capacitor |
| Filter Switch Type      | DPST                 |
| Filtering Requirements  | Filtered             |
| Output Termination Type | Terminal Block       |
| Ground Choke Option     | No                   |

Configuration Features

|              |      |
|--------------|------|
| Fuse Options | Dual |
|--------------|------|

Electrical Characteristics

|                      |             |
|----------------------|-------------|
| Inductance L1        | .32 $\mu$ H |
| Capacitance Cx1      | 220         |
| Overvoltage Category | II          |
| Current Rating (Max) | 10 A        |



|                                      |      |
|--------------------------------------|------|
| Leakage Current (Max) (120VAC, 60Hz) | 0 µA |
| Leakage Current (Max) (250VAC, 50Hz) | 0 µA |

Body Features

|                |                |
|----------------|----------------|
| Product Weight | 154 g[5.43 oz] |
|----------------|----------------|

Dimensions

|                |                  |
|----------------|------------------|
| Product Width  | 49.8 mm[1.96 in] |
| Product Length | 32 mm[1.25 in]   |
| Product Height | 93 mm[3.66 in]   |

Operation/Application

|                |                    |
|----------------|--------------------|
| Cooling Method | Natural Convection |
|----------------|--------------------|

Industry Standards

|                  |                                                                                |
|------------------|--------------------------------------------------------------------------------|
| Certified To     | CSA 22.2 No. 8 1986, EN 60320, EN 60601-1, EN 60939, EN 60950, UL 1283, UL 544 |
| Pollution Degree | PD2                                                                            |
| IP Rating        | IP40                                                                           |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                  |
|-----------------------------------------------|------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions                                        |
| EU ELV Directive 2000/53/EC                   | Not Yet Reviewed                                                 |
| China RoHS 2 Directive MIIT Order No 32, 2016 | 未针对中国 RoHS 符合性进行审核 Not reviewed for China RoHS compliance        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2025 (250)<br>Not Yet Reviewed |
| Halogen Content                               | Not Yet Reviewed for halogen content                             |
| Solder Process Capability                     | Not reviewed for solder process capability                       |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished



product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



## Also in the Series | Schaffner FN9290



## Documents

### CAD Files

#### Customer View Model

ENG\_CVM\_CVM\_816751-SF\_G.3d\_igs.zip

English

#### Customer View Model

ENG\_CVM\_CVM\_816751-SF\_G.2d\_dxf.zip

English

#### Customer View Model

ENG\_CVM\_CVM\_816751-SF\_G.3d\_stp.zip

English

### 3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### Power Entry Module with EMC Filter FN9290

English



Agency Approvals

CB SE-68739M1

English