




EMI & EMC Solutions > IEC Inlets > Inlet Filters > FN2660



Filtering Requirements: **Unfiltered**

Current Rating (Max): **10 A**

Output Termination Type: **Litz Wire**

Pollution Degree: **PD2**

IP Rating: **IP00**

[All FN2660 \(17\)](#)

Features

Product Type Features

Filter Type	IEC Inlet Filter
Level Of Filtering	Inductor & Capacitor
Filtering Requirements	Unfiltered
Output Termination Type	Litz Wire

Electrical Characteristics

Capacitance Cy1	2.2
Capacitance Cy2	2.2
Inductance L1	8.3 μ H
Inductance L2	8.3 μ H
Capacitance Cx1	1
Capacitance Cx2	.47
Electrical Resistance to Ground	680 k Ω
Overvoltage Category	II
Current Rating (Max)	10 A
Leakage Current (Max) (120VAC, 60Hz)	200 μ A
Leakage Current (Max) (250VAC, 50Hz)	350 μ A



Body Features

Product Weight	480 g[16.93 oz]
----------------	-----------------

Dimensions

Product Width	73 mm[2.87 in]
Product Length	184.7 mm[7.27 in]
Product Height	35 mm[1.37 in]

Operation/Application

Cooling Method	Natural Convection
Operating Altitude (Max)	2000 m

Industry Standards

Certified To	GB/T 15287, IEC/EN 60939, UL 60939-3
Pollution Degree	PD2
IP Rating	IP00
UL Flammability Rating	UL 94V-0

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An



Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




TE Part # 816597-SF
IL13-US2-SJT-3130-300-S

Also in the Series | Schaffner FN2660



Inlet Filters(17)

Customers Also Bought



TE Part #216396-000
22759/33-30-9



TE Part #CSE-SGAM-610-SGFB
SMA to SMA 610mm RG316



TE Part #206508-1
TYPE XII KEYING PLUG



TE Part #206799-2
RECEPT ASSY,15 POSN,AMPLIMITE



TE Part #3-640426-4
04P MTA156 CONN ASSY 18AWG
ORA



TE Part #1871132-3
DYNAMIC D7 SOCKET CONT ASSY
AG PL #10-12



TE Part #4-2176230-4
3522 3K3 5% 3W



TE Part #1-2176326-3
CRGP 0603 100R 1%



Documents

Product Drawings
FN2660-10-07-C0909
English

Datasheets & Catalog Pages
IEC Inlet Filters FN2660
English

Agency Approvals
CB_Cert_SE-108631
English