




Terminals & Splices > Special Purpose Terminals



Special Purpose Terminal Type: **Bobbin**

Wire Size: **.3 – .9 mm²**

Terminal Material Thickness: **.3 mm [.012 in]**

Terminal Plating Material: **Tin**

Features

Product Type Features

Wire Insulation Support Retention Type	Non-Insulation Support
Sealable	No

Contact Features

Barrel Type	Open
Special Purpose Terminal Type	Bobbin
Terminal Plating Material	Tin
Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	.3 – .9 mm ²
Terminal Material Thickness	.3 mm[.012 in]
Product Length	10.29 mm[.405 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------



Packaging Features

Packaging Quantity	15000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought

TE Part #60713-1
FASTON 250 REC 18-14 AWG BR

TE Part #63945-1
BOBBIN TERMINAL TAB TPCUBR

TE Part #643428-2
12P UMNL HDR ASSY POL

TE Part #794783-1
04P UMNL HDR ASSY,BLACK



TE Part #2-1474654-8
FSN-21.5A-5




TE Part #2-1803060-2
ANVIL, COMBINATION, END FEED




TE Part #1-1877285-2
12P EP SHRD HDR ASMY, WHITE



TE Part #2311844-2
PCB TERMINAL, LOOSE PIECE



TE Part #6474561-1
FSN-23.25Z-16



TE Part #1-238005-1
ANVIL

Documents

Product Drawings

BOBBIN TERMINAL 22-18 AWG TPCUBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_62804-2_M.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_62804-2_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_62804-2_M.3d_igs.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.