




**Power Triple Lock**

TE Internal #: 8-2232263-2

2 Position, Cap, Housing, Crimp, Wire-to-Wire, UL 94V-0, 6 mm [.236 in] Centerline, 1 Row, 600 VAC, Wire & Cable, Power, Power Triple Lock

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors > POWER TRIPLE LOCK: Glow Wire Cap



- Connector Product Type: **Housing**
- Connector & Housing Type: **Cap**
- Termination Method to Wire & Cable: **Crimp**
- Connector System: **Wire-to-Wire**
- Contact Retention Within Housing: **Without**

[All POWER TRIPLE LOCK: Glow Wire Cap \(44\)](#)

**Features**

**Product Type Features**

Connector Product Type	Housing
Connector & Housing Type	Cap
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

**Configuration Features**

Number of Positions	2
Number of Rows	1
Number of Power Positions	2

**Electrical Characteristics**

Operating Voltage	600 VDC
-------------------	---------

**Body Features**



Connector & Keying Code	D
Primary Product Color	Orange
Cable Exit Angle	180 °

#### Contact Features

Contact Layout	Inline
Contact Retention Within Housing	Without
Contact Type	Tab

#### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

#### Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Latches
Connector Mounting Type	Panel Mount

#### Housing Features

Centerline (Pitch)	6 mm [.236 in]
Housing Material	Nylon GF

#### Dimensions

Panel Thickness (Recommended)	1 – 2 mm [.039 – .079 in]
Connector Height	14.95 mm

#### Usage Conditions

Operating Temperature Range	-55 – 140 °C [-67 – 284 °F]
-----------------------------	-----------------------------

#### Operation/Application

Circuit Application	Power
---------------------	-------

#### Identification Marking

Circuit Identification Feature	With
--------------------------------	------

#### Industry Standards

Compatible With Agency/Standards Products	UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-0
Glow Wire Rating	GWT 750°C (Without Flame)



### Packaging Features

Packaging Method	Carton
------------------	--------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 1971789-1  
CPA



TE Part # CAT-P87074-T111  
Tab Contact — POWER TRIPLE LOCK



TE Part # 1971777-2  
PTL TPA HIGH TEMP 1 x 2 BLACK



TE Part # 8-2232265-2  
PTL 1X2 PLUG HSG GLW WIRE KEY D ORA

### Also in the Series | [Power Triple Lock](#)



Connector Contacts(26)



Connector Hardware(12)



Insertion & Extraction Tools(1)




PCB Headers & Receptacles(21)



Power Contacts(26)



Rectangular Power Connectors(301)




Wire-to-Board Headers & Receptacles (21)

## Customers Also Bought



TE Part #4-2600020-3  
XRC PIN TERMINAL 16-20AWG Gold Plated



TE Part #447192-4  
3 ROW BOX RECP 150 POS 100 C/L



TE Part #1-1803079-2  
ANVIL



TE Part #3-1971775-3  
PTL 2X3 CAP PANEL MT STD TEMP KEY C BLU




TE Part #CAT-P87074-T111  
Tab Contact — POWER TRIPLE LOCK




TE Part #8-2232263-4  
PTL 1X4 CAP PANEL MT GLW WIRE KEY D ORA



TE Part #2325347-2  
Power Versa-Lock INTERFACE SEAL, 1X2



TE Part #5677588077  
RNF-3000-9/3-0-1M



TE Part #2119757-2  
DEPRESSOR, SHEAR

## Documents



## Product Drawings

[PTL 1X2 CAP PANEL MT GLW WIRE KEY D ORA](#)

English

---

## CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_8-2232263-2\\_B.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_8-2232263-2\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_8-2232263-2\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

## Product Specifications

[Application Specification](#)

English

---

## Agency Approvals

[VDE Certificate](#)

English