



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **Natural**

Primary Product Material: **Polyester**

Number of Positions: **8**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Product Profile	Standard
Connector Cover Type	Strain Relief Cover

Configuration Features

Number of Positions	8
---------------------	---

Body Features

Primary Product Color	Natural
Primary Product Material	Polyester

Mechanical Attachment

Strain Relief	With
---------------	------

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
--------------------	------------------

Usage Conditions

Compatible With IDC Installation Type Connector	Closed End
Operating Temperature (Max)	105 °C[221 °F]



Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 3-641150-8
08P MTA156 ASSY 22AWG RED LF



TE Part # 3-641218-8
08P MTA156 CONN ASSY 20AWG LF



TE Part # 3-644462-8
08P MTA156 CONN ASSY 20AWG LF




TE Part # 3-647479-8
08P MTA156 CONN ASSY 18AWG ORA







TE Part # 2-647123-8
08P MTA156 SHRD HDR ASSY SQ SN




TE Part # 3-641119-8
08P MTA156 HDR ASSY FL/ST LF



TE Part # 3-641121-8
08P MTA156 HDR ASSY FL/RA LF



TE Part # 3-640429-8
08P MTA156 CONN ASSY 24AWG WHT



TE Part # 3-643820-8
08P MTA156 CONN ASSY 24AWG LF



TE Part # 3-644467-8
08P MTA156 CONN ASSY 22AWG LF




TE Part # 3-644760-8
08P MTA156 HDR ASSY FL ST LF




TE Part # 3-644661-8
08P MTA156 HDR ASSY POL W/O#2




TE Part # 3-644617-8
08P MTA156 HDR ASY PO RA FB LF




TE Part # 3-641202-8
08P MTA156 HDR ASSY PL 30AU LF




TE Part # 3-644615-8
08P MTA156 POL HDR ASSY LF




TE Part # 644751-8
08P MTA156 HDR ASSY R/A



TE Part # 644753-8
08P MTA156 HDR ASSY RN STR F/L



TE Part # 641922-2
08P MTA156 HDR ASSY STR W/O#3



TE Part # CAT-103156-WBHSM
Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156



TE Part # 2-647127-8
08P MTA156 SHRD HDR ASSY LF

Also in the Series | **MTA 156**




Connector Caps & Covers(89)



Connector Contacts(4)




Connector Hardware(2)



Power Contacts(3)



[Rectangular Power Connectors\(1178\)](#)



[Standard Rectangular Connectors\(667\)](#)



[Wire-to-Board Connector Assemblies & Housings\(594\)](#)

Customers Also Bought




TE Part #817050-SF
[FN2010N1-10-06](#)




TE Part #66098-6
[III+ PIN,18-16,30AU>10,STRIP](#)




TE Part #1-66358-3
[III+ SKT,18-14,30AU/FL,STRIP](#)



TE Part #2-640550-0
[20P MTA100 COVER](#)



TE Part #640551-3
[03P MTA156 COVER](#)



TE Part #1-640551-6
[16P MTA156 COVER](#)



TE Part #3-641119-5
[05P MTA156 HDR ASSY FL/ST LF](#)



TE Part #1658622-9
[40 NOVO MIL/CTR 30DP,LEAD FREE](#)



TE Part #1-6609028-3
[10VK1=F7143 S0](#)



TE Part #6609032-9
[5VR1=F7202 S0](#)

Documents

Product Drawings

[08P MTA156 COVER](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_640551-8_G.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_640551-8_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_640551-8_G.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_640551-8_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_640551-8_L.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_640551-8_L.2d_dxf.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

Japanese

[Application Specification](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

Japanese