8-35247-2 ✔ ACTIVE


SOLISTRAND

TE Internal #: 8-35247-2

Closed Ring Tongue Terminal, 8 AWG, 1/4 / M6 Stud, 6.35 mm [.25 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, Uninsulated

View on TE.com >

Terminals & Splices > Ring Terminals



Ring Terminal Product Type: **Closed Ring Tongue Terminal**

Wire Size: **13100 – 20800 CMA**

Stud Size: **1/4, M6**

Features

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	1/4, M6
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Holes	1

Body Features

Product Weight	3.78 g

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	Without

Dimensions

Wire Size	13100 – 20800 CMA
Stud Diameter	6.35 mm[.25 in]
Tongue Thickness	1.22 mm[.05 in]
Product Length	29.67 mm[1.17 in]
Barrel Inside Diameter	4.37 mm[.172 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	0 – 170 °C[0 – 338 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No

Packaging Features

Packaging Quantity	50
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent

chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 69355
HHHT SOLIS SOLIS FLAG STRATO 8 ASSY

Customers Also Bought



TE Part #CW2823-000
R85049/128-3



TE Part #32996-1
TERMINAL, SOLIS R 8 8



TE Part #329966
SOLIS R 22-16COMM 22-18MIL 1/2



TE Part #1445715-3
75A HSG SUBASY WHITE



TE Part #1-1600961-8
CONT 12-16 AWG PWR, STD PLATE



TE Part #1658672-1
HDP-22,PLUG,SIZE 3,44 POSN



TE Part #1658683-1
HDP-22,RCPT,SIZE 3,44 POSN



TE Part #5102159-2
A/L UNIV HDR 14P RA



TE Part #5531216-5
CONTACT MINI TANDEM SPRING L



TE Part #11027934-00
44032RC,THERM,ROHS

Documents

Product Drawings

TERMINAL,SOLIS R 8 1/4

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_8-35247-2_U.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_8-35247-2_U.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_8-35247-2_U.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

SOLISTRAND - QRG

English

Instruction Sheets

Instruction Sheet (U.S.)

English