




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – .82 mm²**

Mating Tab Width: **7.92 mm [.312 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	7.92 mm[.312 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Flag
Contact Base Material	Brass
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple
Extraction Force	.7 – 10.2 kgf

Dimensions

Product Length	18.3 mm[.72 in]
Compatible Insulation Diameter Range	1.52 – 2.31 mm[.06 – .091 in]
Terminal Material Thickness	.33 mm[.013 in]
Wire Size	.51 – .82 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Quantity	2000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 177720-2
312 POSITIVE FLAG HSG 3P




TE Part # 172615-2
POSITIVE LOCK 312 HOUSING RECEPTACLE



TE Part # 353752-2
HEAD LAMP CONNECTOR .312 (7.92 MM)

Also in the Series | Positive Lock 312



Crimp Terminal Housings(3)



Insertion & Extraction Tools(1)



Quick Disconnects(5)


Customers Also Bought



TE Part #170037-2
187 FASTON,REC.,20-16 AWG,TPBR



TE Part #170140-2
187 FASTON,FLAG,REC.,16-20 AWG, TPBR



TE Part #CAT-472-Z12
Hard Metric Male Connector: Traditional Backplane, Mezzanine, 2mm



TE Part #6-1393127-1
PRD-11DY0-12=PRD



Documents

Product Drawings

PL 312 FLAG REC 20-18AWG 0.32X24.9 PTPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_900319-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_900319-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_900319-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

.312 Series Positive Lock Receptacle (Flag)

English

Instruction Sheets

Instruction Sheet (non U.S.)

Japanese