



MATE-N-LOK | Commercial MATE-N-LOK

TE Internal #: 925076-3

4 Position, Plug, Housing, Crimp, Wire-to-Wire, UL 94V-2, 5.08 mm [.2 in] Centerline, 2 Row, 250 VAC, Wire & Cable, Commercial MATE-N-LOK

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**

Connector & Housing Type: **Plug**

Termination Method to Wire & Cable: **Crimp**

Connector System: **Wire-to-Wire**

Contact Retention Within Housing: **Without**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	2

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

--	--



Contact Retention Within Housing	Without
----------------------------------	---------

Contact Type	Socket
--------------	--------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	Without
---------------------	---------

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	5.08 mm [.2 in]
--------------------	-----------------

Housing Material	PA 66
------------------	-------

Dimensions

Row-to-Row Spacing	5.08 mm [.2 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Identification Marking

Circuit Identification Feature	Without
--------------------------------	---------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

UL Rating	Certified, Recognized
-----------	-----------------------

Compatible With Approved Standards Products	UL E28476
---	-----------

CSA Rating	LR 16455
------------	----------

UL Flammability Rating	UL 94V-2
------------------------	----------

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------

Packaging Features

Packaging Quantity	500
--------------------	-----

Packaging Method	Bag
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 925076-6
4W CIRCULAR MATE-N-LOK SOCKET HSG NAT



TE Part # 925075-3
4W CIRCULAR MATE-N-LOK PIN HSG BLK



TE Part # 925075-7
4W CIRCULAR MATE-N-LOK PIN HSG NAT



TE Part # 925075
4W CIRCULAR MATE-N-LOK PIN HSG NAT



TE Part # 925076-7
4W CIRCULAR MATE-N-LOK SOCKET HSG NAT

Also in the Series | Commercial MATE-N-LOK



Connector Contacts(150)



Crimp Wire Pins, Tabs & Ferrules(2)



Power Contacts(146)




Rectangular Connector Housings(118)



Rectangular Power Connectors(181)




Standard Circular Connectors(2)



Standard Rectangular Connectors(126)


Customers Also Bought



TE Part #NB09542001
ATUM-16/4-0-STK



TE Part #163302-6
MATENLOK SIDE WAY




TE Part #8-215079-6
MICRO-MATCH FOB.16P



TE Part #480487-4
187 FASTON FLAG INSL POD NYLON LP NAT




TE Part #5-534267-2
20 MODIV VRT DR DE 100/125



TE Part #1217169-1
250 FASTON,PCB TAB,TCBR




TE Part #1825057-3
ADE0404=DIP SWITCH,EXT,THRU/HL



TE Part #9-6474612-2
FSN-22A-6



TE Part #534267-2
20 MODIV VRT DR OE 100/125



TE Part #7-1437139-7
FSN-21A-15=NOMEX FS STD

Documents



Product Drawings

4W CIRCULAR MATE-N-LOK SOCKET HSG BLK

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_925076-3_G.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_925076-3_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_925076-3_G.3d_stp.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_925076-3_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_925076-3_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_925076-3_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English