




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**
Connector & Housing Type: **Cap**
Termination Method to Wire & Cable: **Crimp**
Connector System: **Wire-to-Panel, Wire-to-Wire**
Contact Retention Within Housing: **Without**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Cap
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1
Number of Power Positions	0
Number of Signal Positions	0

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------



Contact Features

Multiple Contact Types	Without
Contact Layout	Inline
Contact Retention Within Housing	Without
Contact Type	Pin

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Latches
Connector Mounting Type	Panel Mount

Housing Features

Centerline (Pitch)	6.35 mm[.25 in]
Housing Material	PA 6

Dimensions

Panel Thickness (Recommended)	.76 – 2.29 mm[.03 – .09 in]
-------------------------------	-----------------------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL, VDE
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	Certified, LR 7189
UL Flammability Rating	UL 94V-2
Glow Wire Rating	GWT 750°C (Without Flame)

Packaging Features

Packaging Quantity	2000
Packaging Method	Bag



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1703062-2
CAP, 2 CIRCUIT , UNIVERSAL MATE-N-LOK




TE Part # 350779-1
04P UMNL PLUG HSG



TE Part # 794783-3
04P UMNL HDR ASSY,BLACK LF



TE Part # 1-350944-0
04P UMNL HDR ASSY R/A 94VO



TE Part # 1703062-3
CAP, 2 CIRCUIT , UNIVERSAL MATE-N-LOK



TE Part # 1586086-1
04P UMNL PIN HDR ASSY W/O DRNS



TE Part # 1-480702-0
04P UMNL PLUG HSG NATL



TE Part # 1-480702-9
04P UMNL PLUG HSG BLK



TE Part # 350826-1
04P UMNL HDR ASSY PC 94VO



TE Part # 350988-4
04P UMNL HDR ASSY LNG/TL



TE Part # 350833-1
04P UMNL HDR ASSY PC 94VO



TE Part # 350430-4
04P UMNL PIN HDR ASSY NATL LF



TE Part # 350793-3
04P UMNL PIN HDR ASSY 94VO LF



TE Part # 1586163-1
04P UMNL PIN HDR 94VO NDH



TE Part # 643230-1
04P UMNL HDR ASSY R/A 94VO



TE Part # 794783-1
04P UMNL HDR ASSY,BLACK



TE Part # 926682-1
UNIVERSAL M-N-L CAP 6 POS



TE Part # 641968-1
04P UMNL PIN HDR ASSY POL 94VO



TE Part # 1586963-1
04P UMNL PIN HDR ASSY, GW



TE Part # 173926-1
4 P ACTION PIN UMNL


Also in the Series | **Universal MATE-N-LOK**



Circular Power Connectors(2)



Connector Contacts(205)



Connector Hardware(12)



Power Contacts(205)




[Rectangular Power Connectors\(644\)](#)



[Standard Circular Connectors\(1\)](#)

Customers Also Bought



TE Part #596381-000
[B-106-1602](#)



TE Part #34853
[TERMINAL,PG R 12-10 8](#)



TE Part #163305-2
[MATENLOK PIN SDW](#)



TE Part #163306-2
[MATENLOK SOCK](#)



TE Part #163307-2
[MATENLOK PIN](#)



TE Part #1-770904-1
[MINI UMNL SOK 22-18AWG AU LF](#)



TE Part #1-794606-1
[MICRO MNL RPT CNT STRP 15AU LF](#)



TE Part #926682-3
[06P UNIV.M-N-L.HSG.](#)



TE Part #6-1623933-7
[CFR50 5% 820R](#)



TE Part #1745078-1
[AMP MCP 2.8K - REC. HOUSING](#)

Documents

Product Drawings

[UNML4WAY CAP](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_926305-6_H.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_926305-6_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_926305-6_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[VDE Certificate](#)

English

[VDE Certificate](#)

English