




Automotive Parts > Automotive Connectors > Automotive Housings > Timer Connector Housing



Nominal Voltage Architecture: 240 V

Connector & Housing Type: Housing for Male Terminals

Number of Positions: 2

Sealable: No

Operating Temperature Range: -55 – 105 °C [-67 – 221 °F]

[All Timer Connector Housing \(436\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Male Terminals
Sealable	No
Primary Locking Feature	Locking Lance
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	240 VAC
-------------------	---------



Nominal Voltage Architecture	240 V
Body Features	
Primary Product Color	Black
Connector & Keying Code	Neutral
Contact Features	
Contact Size	5.8mm
Contact Type	Tab
Mating Tab Width	5.8 mm[.23 in]
Contact Current Rating (Max)	40 A
Mechanical Attachment	
Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Polarizing Slot
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Housing Material	Nylon 6/6
Centerline (Pitch)	8.6 mm[.33 in]
Dimensions	
Product Width	35.5 mm[1.39 in]
Product Length	30.6 mm[1.2 in]
Connector Height	35.5 mm[1.398 in]
Usage Conditions	
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Operating Temperature (Max)	105 °C[221 °F]
Operation/Application	
Circuit Application	Power
Industry Standards	
UL Flammability Rating	UL 94HB
Packaging Features	
Packaging Quantity	1500



Packaging Method	Tray
Other	
Serviceable	No
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1-968050-1
SPECIAL TERMINAL 11-10 AWG PTPB



TE Part # 965665-1
STD-POW-TIM GEH 2P



Also in the Series | Timer Connector System



Automotive Connector Locks & Position Assurance(15)




Automotive Housings(186)




Automotive Seals & Cavity Plugs(32)



Automotive Signal & Power Connector Housings(136)



Crimp Terminal Housings(13)



Other Automotive Connector Accessories(1)

Customers Also Bought



TE Part #K1142143
Relay 29-011-11A




TE Part #5053196254
RNF-100-1/2-0-35MM




TE Part #CAT-T4827-CH8172
Timer Connector Housing



TE Part #1-967630-3
FLACHSTE-GEH2,8 21P



TE Part #967633-1
2. KONT-SICHERUNG 15P



TE Part #9-1394050-1
COVER F.21P REC-HSG



TE Part #1-1418469-1
6POS,AMP MCP1.5K,REC. HSG,CODA



TE Part #1563111-1
COVER,180



TE Part #368376-1
81P REC HSG ASSY() BLK



Documents

Product Drawings

FLACH-KONT-GEH 2P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_965664-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_965664-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_965664-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English