

FN372-2-31 ✓ ACTIVE

Schaffner | Schaffner FN370


TE Internal #: 800188-SF

2 A, Filtered, FASTON, 373 μ A Leakage Current @ 120VAC, 60Hz,
PD2 Pollution Degree, IP40, UL 94V-2, Schaffner FN370, Inlet Filters

[View on TE.com >](#)



EMI & EMC Solutions > IEC Inlets > Inlet Filters > Power Entry Module with EMC Filter FN370, Versatile Filtered Power Entry Solution



Filtering Requirements: **Filtered**

Current Rating (Max): **2 A**

Output Termination Type: **FASTON**

Pollution Degree: **PD2**

IP Rating: **IP40**

[All Power Entry Module with EMC Filter FN370, Versatile Filtered Power Entry Solution \(55\)](#)

Features

Product Type Features

| | |
|-------------------------|----------------------|
| Level Of Filtering | Inductor & Capacitor |
| Filtering Requirements | Filtered |
| Output Termination Type | FASTON |

Configuration Features

| | |
|--------------|------|
| Fuse Options | Dual |
|--------------|------|

Electrical Characteristics

| | |
|--------------------------------------|------------------------|
| Capacitance Cy1 | 2.2 |
| Inductance L1 | .7 μ H |
| Capacitance Cx1 | 47 |
| Input Voltage Selection | Dual AC Voltage (SMPS) |
| Oversvoltage Category | II |
| Current Rating (Max) | 2 A |
| Leakage Current (Max) (120VAC, 60Hz) | 373 μ A |

Body Features

| | |
|----------------|---------------|
| Product Weight | 55 g[1.94 oz] |
|----------------|---------------|

Dimensions

| | |
|----------------|------------------|
| Product Width | 58 mm[2.28 in] |
| Product Length | 32 mm[1.25 in] |
| Product Height | 59.5 mm[2.34 in] |

Operation/Application

| | |
|----------------|--------------------|
| Cooling Method | Natural Convection |
|----------------|--------------------|

Industry Standards

| | |
|------------------------|--|
| Certified To | CSA 22.2 No. 8 1986, IEC/EN 60939, UL 1283 |
| Pollution Degree | PD2 |
| IP Rating | IP40 |
| UL Flammability Rating | UL 94V-2 |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Not Yet Reviewed |
| China RoHS 2 Directive MIIT Order No 32, 2016 | 有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2025 (250) Not Yet Reviewed |
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the

product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Also in the Series | Schaffner FN370



Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_800188-SF_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_800188-SF_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_800188-SF_B.3d_igs.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Power Entry Module with EMC Filter FN370

English

Agency Approvals

VDE Certificate



English