




TE Internal #: T4062113004-005

M8 to M8 Cable Assembly, 4 Position, Cable Assembly Length 5 m [16.4 ft], Sensor/Actuator, A Code, M8 Plug End A, M8 Socket End B, Shielded

[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M8 Male Straight to Female Straight Double Ended Cable



Cable Assembly Length: 5 m [16.4 ft]

M8/M12 Application Type: **Sensor/Actuator**

Number of Positions: 4

Connector & Keying Code: **A**

Cable Assembly Type: **M8 to M8**

[All M8 Male Straight to Female Straight Double Ended Cable \(55\)](#)

Features

Product Type Features

Cable Assembly Type	M8 to M8
Cable Assembly (End A)	M8 Plug
Cable Assembly (End B)	M8 Socket

Configuration Features

Number of Positions	4
---------------------	---

Electrical Characteristics

Operating Voltage	30 VDC
-------------------	--------

Body Features

Connector Color (End B)	Black
Jacket Material	PVC
Connector Color (End A)	Black
Conductor Material	Copper Alloy
Cable Color	Black



Wire Color (Base)	Brown, White, Blue, Black
Connector & Keying Code	A

Contact Features

Contact Current Rating (Max)	3 A
------------------------------	-----

Mechanical Attachment

Thread Size	M8 x M8
Connector Orientation (End A)	Straight
Connector Orientation (End B)	Straight

Housing Features

Housing Material	Nylon GF
------------------	----------

Dimensions

Outside Cable Diameter	5 mm
Wire Size	24 AWG

Operation/Application

M8/M12 Application Type	Sensor/Actuator
Shielded	Yes

Other

Field Serviceable	Yes
Cable Assembly Length	5 m[16.4 ft]
Cable Assembly Configuration	Double Ended

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: Pb (1.9% in 2505725083) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.



Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # T4062213004-005

RPC-M8-4MR-5.0SH-M8-4FS-PVC

Customers Also Bought

TE Part #T4061120003-005

M8 CABLE ST M 5M 3POS PUR CABLE

TE Part #T4062113004-001

RPC-M8-4MS-0.5SH-M8-4FS-PVC

TE Part #T4131012041-000

M12,REAR MOUNT,FEMALE,A,4P, SOLDER WIRE

TE Part #CAT-C73765-M1A

M8 Panel Mount Solder Cups

TE Part #CAT-C73765-M1B

M8 Panel Mount Wire

TE Part #6-102316-3

MOD IV RECP LP LF

TE Part #770069-1

02P .093 COMM P&S PLUG .248CL

TE Part #1-1609112-3

15CBS1=F8273

Documents



Product Drawings

RPC-M8-4MS-5.0SH-M8-4FS-PVC

English

CAD Files

Customer View Model

ENG_CVM_CVM_T4062113004-005_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T4062113004-005_B.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_T4062113004-005_B.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English

Agency Approvals

UL

English