

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
—	—		A	REVISED PER ECR-10-023099	16NOV10	HMR DD

D

C

B

A

D

C

B

A




- 1

HIGH CONDUCTIVITY COPPER ALLOY, 0.30[.012]THK.
- 2


WIRE RANGE: 3-6mm² [12-10 AWG].
- 3


DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4

PRE-TIN PLATED.



SECTION A-A
SCALE 10:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN		16OCT2008		FINISH		MATERIAL		2058931-1	
		CHK D FLEMING		16OCT2008		APVD —		NAME		PART NUMBER	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		PRODUCT SPEC —		Tyco Electronics Corporation Harrisburg, PA 17105-3608 SOCKET, UNIVERSAL MATE-N-LOK(TM) II					
				APPLICATION SPEC —							
MATERIAL —				WEIGHT —		SIZE A2	CAGE CODE 00779	DRAWING NO C-2058931		RESTRICTED TO —	
				CUSTOMER DRAWING		SCALE 4:1		SHEET 1 of 1		REV A	