









AMP		AMP Deutschland GmbH D - 63225 Langen	
NAME			
HV100 RECEPTACLE CONNECTOR, SMD WITH ADAPTER PACKED IN BLISTER BELT			
SIZE / CASE CODE		DRAWING NO. ZEICHNUNGS-NR.	RESISTED TO NUR FUER
A200779		C-969973	—
KUNDENZEICHNUNG		MASSSTAB 1:1	BLATT 1 OF 2 REV C2

1																				5	HV100 CONNECTOR, SMD, 2x20P05. HV100 BUCHSENSTECKER, SMD, 2x20 POL.	2-966 737-0		
	1																			5	HV100 CONNECTOR, SMD, 2x19P05. HV100 BUCHSENSTECKER, SMD, 2x19 POL.	1-966 737-9		
		1																		5	HV100 CONNECTOR, SMD, 2x18P05. HV100 BUCHSENSTECKER, SMD, 2x18 POL.	1-966 737-8		
			1																	5	HV100 CONNECTOR, SMD, 2x17P05. HV100 BUCHSENSTECKER, SMD, 2x17 POL.	1-966 737-7		
				1																5	HV100 CONNECTOR, SMD, 2x16P05. HV100 BUCHSENSTECKER, SMD, 2x16 POL.	1-966 737-6		
					1															5	HV100 CONNECTOR, SMD, 2x15P05. HV100 BUCHSENSTECKER, SMD, 2x15 POL.	1-966 737-5		
						1														5	HV100 CONNECTOR, SMD, 2x14 P05. HV100 BUCHSENSTECKER, SMD, 2x14 POL.	1-966 737-4		
							1													5	HV100 CONNECTOR, SMD, 2x13 P05. HV100 BUCHSENSTECKER, SMD, 2x13 POL.	1-966 737-3		
								1												5	HV100 CONNECTOR, SMD, 2x12 P05. HV100 BUCHSENSTECKER, SMD, 2x12 POL.	1-966 737-2		
									1											5	HV100 CONNECTOR, SMD, 2x11 P05. HV100 BUCHSENSTECKER, SMD, 2x11 POL.	1-966 737-1		
										1										5	HV100 CONNECTOR, SMD, 2x10 P05. HV100 BUCHSENSTECKER, SMD, 2x10 POL.	1-966 737-0		
											1									5	HV100 CONNECTOR, SMD, 2x9 POS. HV100 BUCHSENSTECKER, SMD, 2x9 POL.	966 737-9		
												1								5	HV100 CONNECTOR, SMD, 2x8 POS. HV100 BUCHSENSTECKER, SMD, 2x8 POL.	966 737-8		
													1							5	HV100 CONNECTOR, SMD, 2x7 POS. HV100 BUCHSENSTECKER, SMD, 2x7 POL.	966 737-7		
														1						5	HV100 CONNECTOR, SMD, 2x6 POS. HV100 BUCHSENSTECKER, SMD, 2x6 POL.	966 737-6		
															1					5	HV100 CONNECTOR, SMD, 2x5 POS. HV100 BUCHSENSTECKER, SMD, 2x5 POL.	966 737-5		
																1				5	HV100 CONNECTOR, SMD, 2x4 POS. HV100 BUCHSENSTECKER, SMD, 2x4 POL.	966 737-4		
																	1			5	HV100 CONNECTOR, SMD, 2x3 POS. HV100 BUCHSENSTECKER, SMD, 2x3 POL.	966 737-3		
																		1		5	HV100 CONNECTOR, SMD, 2x2 POS. HV100 BUCHSENSTECKER, SMD, 2x2 POL.	966 737-2		
1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1		4	ADAPTER	LCP	BLACK SCHWARZ	
																			1	4	ADAPTER	LCP	BLACK SCHWARZ	
																				3	COVER TAPE 65.4mm ABDECKFOLIE 65.4mm	PET	TRANSPARENT	
																				3	COVER TAPE 49.4mm ABDECKFOLIE 49.4mm	PET	TRANSPARENT	
																				3	COVER TAPE 37.4mm ABDECKFOLIE 37.4mm	PET	TRANSPARENT	
																				3	COVER TAPE 25.4mm ABDECKFOLIE 25.4mm	PET	TRANSPARENT	
																				2	BLISTER BELT 72mm BLISTERGURT 72mm	PS	GREY GRAU	
																				2	BLISTER BELT 56mm BLISTERGURT 56mm	PS	GREY GRAU	
																				2	BLISTER BELT 44mm BLISTERGURT 44mm	PS	GREY GRAU	
																				2	BLISTER BELT 32mm BLISTERGURT 32mm	PS	GREY GRAU	
																				1	REEL ø330/150x78.4 REEL ø330/150x78.4	PS	GREY GRAU	
																				1	REEL ø330/150x62.4 REEL ø330/150x62.4	PS	GREY GRAU	
																				1	REEL ø330/100x50.4 REEL ø330/100x50.4	PS	GREY GRAU	
																				1	REEL ø330/100x38.4 REEL ø330/100x38.4	PS	GREY GRAU	
2--0	1--9	1--8	1--7	1--6	1--5	1--4	1--3	1--2	1--1	1--0	-9	-8	-7	-6	-5	-4	-3	-2	POS.	DESCRIPTION BENENNUNG		SURFACE OBERFLAECHE COLOUR/FARBE	MATERIAL	

DETAIL X
EINZELHEIT X



ABWICKELRICHTUNG
DIRECTION OF THE TOP
OF THE REEL



740 669-4	④
740 713-1	③
740 669-2	②
740 715-1	①
BLISTER PN:	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. DIESSES ZEICHNUNGSDOKUMENT WIRD DURCH AMP INCORPORATED KONTROLLIERT. ÄNDERUNGEN, DIE DEN TECHNISCHEN FORTSCHRITT DIENTEN, SIND VORBEHALTEN. DEN JEWEILS LETZTBESTEHENDEN ÄNDERUNGSSTAND BEFOLGEN SIE AUF ANFRAGE.	
DIMENSIONS: mm	OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN P: ISO 8015 P: ISO 2768 - mH - E P: DIN 16901 - 140
	0 PLC ±0.2 1 PLC ±0.1 2 PLC ±0.1 3 PLC ±0.1
MATERIAL SEE TABLE SIEHE TABELLE	ANGLES/WINKEL ±° FINISH/OBERFLÄCHE/FARBE SEE TABLE SIEHE TABELLE

DWN M. STEIN 18-MAR-98	CHK F. REICHARDT 18-MAR-98
APVD G. Feldmeier	- NAME
PRODUCT SPEC PRODUKTSPEZ.	APPLICATION SPEC VERARBEITUNGSSPEZ.
WEIGHT GEWICHT	CUSTOMER DRAWING /KUNDENZEICHNUNG

AMP AMP Deutschland GmbH D - 63225 Langen	
HV100 RECEPTACLE CONNECTOR, SMD WITH ADAPTER PACKED IN BLISTER BELT	
SIZE A2	CAGE CODE 00779
DRAWING NO. ZEICHNUNGS-NR. C-969973	RESTRICTED TO NUR FÜR —
MASSSTAB 2:1	BLATT 2 VON 2
REV C2	