


## 211541-1 Product Details



**211541-1**  
(M24308/2-492F)  
TE Internal Number: 211541-1

Active

View 3D PDF

### Subminiature D Pins/Sockets for MIL-C-24308 and MIL-C-39029

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- Connector
- Product Series = 90
- Connector Style = Receptacle
- Accepts Contact Gender = Socket
- Density = Standard

[View all Features](#)

Add to My Part List Request Sample Find Similar Products Buy Product

### Have a Question?

Chat with a Product Information Specialist



#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [RECEPTACLE ASS'Y.,AMPLIMITE](#), (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version E)
- [3D Model](#) (IGES, Version E)
- [3D Model](#) (STEP, Version E)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Connector
- [Product Series](#) = 90
- [Shell Size](#) = 6
- [Shell Material](#) = Steel
- [Termination Method to Wire/Cable](#) = Crimp

#### Body Related Features:

- [Number of Positions](#) = 104
- [Blindmate](#) = No
- [Non-Magnetic](#) = No
- [Rear Grommet](#) = No
- [Power/Signal/Coax Combination](#) = No
- [Shell Plating](#) = Zinc
- Mount Style = Dual Floating Bushing

#### Contact Related Features:

- Accepts Contact Gender = Socket
- [Contact Size](#) = 22
- [Contact Style](#) = Crimp Snap-in

#### Housing Related Features:

- Connector Style = Receptacle

#### Configuration Related Features:

- [Density](#) = Standard

#### Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M24308/2-492F
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin-in-Paste capable to 245°C, Pin-in-Paste capable to 260°C
- NASA Qualification = No

#### Conditions for Usage:

- Applies To = Wire

#### Other:

- Brand = AMP
- Comment = Without Contact(s)

BOOKMARK

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

### Follow Us On:



### Visit Us On:

