




# 1903813-1 Product Details

[Share](#) | [Print](#) | [Email](#)


## 2.5mm Signal Double Lock Connector

2.5MM SDL 3/5P POST HDR ASSY S

**1903813-1**

TE Internal Number: 1903813-1

Active

[View 3D PDF](#)

### Product Highlights [View All](#)

- Connector
- Wire-to-Board
- Applies To Printed Circuit Board
- Glow Wire Rating = Standard Part - Not Glow Wire
- Header

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

**Please Note:**  
Use the Product Drawing for all design activity

Product Type Features	
Product Type	Connector
Connector Type	Header
Profile	Standard
PCB Mounting Orientation	Vertical
PCB Mount Retention	With
PCB Mount Alignment	With
PCB Mount Retention Type	Kinked
PCB Mount Alignment Type	Boss
Sealed	No

Mechanical Attachment	
Contact Retention	Without
Mating Retention Type	Latch(ing)

Electrical Characteristics	
Contact - Rated Current (A)	3 - 5
Operating Voltage Reference	AC/DC
Operating Voltage (VAC)	50 - 250
Operating Voltage (VDC)	50 - 250

Termination Features	
Termination Method to Wire/Cable	Solder
Termination Method to PC Board	Through Hole - Solder

Dimensions	
Tail Length (mm [in])	3.2 [0.126]
PCB Thickness, Recommended (mm [in])	1.60 [0.063]

Body Features	
Header Type	Shrouded
Mating Retention	With

Contact Features	
Contact Type	Tab
Contact Base Material	Brass
Contact Plating, Mating Area, Material	Pre-Tin
Contact Plating, Mating Area, Thickness (µm [µin])	0.8 - 2.5 [31.49 - 98.42]
Contact Plating, Termination Area, Material	Pre-Tin
Contact Plating, Termination Area, Thickness (µm [µin])	0.8 - 2.5 [31.49 - 98.42]
Underplate Material	Copper
Underplate Material Thickness (µm [µin])	0.50 - 1.20 [19.680 - 47.240]
Contact Size	.64

Housing Features	
Connector Style	Receptacle
Housing Material	Nylon 6/6 GF
Housing Color	Natural
Mating Alignment	With
Mating Alignment Type	Polarization

Configuration Features	
Number of Positions	3
Number of Rows	1
Strain Relief	Without

Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant

Lead Free Solder Processes	Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C
----------------------------	--

RoHS/ELV Compliance History	Always was RoHS compliant
-----------------------------	---------------------------

UL Flammability Rating	UL 94V-0
------------------------	----------

Environmental	
Operating Temperature (°C [°F])	-30 - +105 [-22 - +221]

Conditions for Usage	
Applies To	Printed Circuit Board
Glow Wire Rating	Standard Part - Not Glow Wire

Operation/Application	
Application Use	Wire-to-Board
Contact Transmits (Typical Application)	Signal (Data)

Packaging Features	
Packaging Method	Bag/Box
Packaging Quantity	150

Other	
Brand	TE Connectivity

### Related Products

Not quite the product you're looking for?  
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

**Corporate Information**  
[About TE](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)  
[Terms & Conditions](#)  
[Privacy Policy](#)  
[Global Accessibility Statement](#)

**Quick Links**  
[Distributor Inventory](#)  
[Product Cross Reference](#)  
[Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

**Customer Support**  
[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Knowledge Base](#)  
[Manage Your Account](#)

### Keep Me Informed

