




What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > Product Feature Selector > Product Details

1-1761199-2 Product Details

Share Print Email



1-1761199-2

SDL (Shielded Data Link)

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Receptacle
- Receptacle Configuration = Standard
- Number of Conductors = 6
- Keying = A

[View all Features](#)

Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

TE Internal Number: 1-1761199-2

Active

View 3D PDF

Add to My Part List Request Sample Find Similar Products Buy Product

Documentation & Additional Information

Product Drawings:

- RECEPTACLE ASSEMBLY, SIDE ENTRY, SDL (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- SDL Systemj Connector (PDF, English)

Application Specifications:

- SDL Top-Entry and Side-Entry Printed Circuit (PC) Bo... (PDF, English)

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version B)
- 3D Model (IGES, Version B)
- 3D Model (STEP, Version B)

Additional Information:

- Product Line Information

Related Products:

- Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Gender = Receptacle
- Receptacle Configuration = Standard
- Grounding Options = PCB and Panel Ground
- PCB Mount Retention = With
- PCB Mount Retention Type = Boardlock(s)
- Shield Material = Brass

Body Features:

- Shield Plating = Tin over Nickel

Contact Features:

- Contact Base Material = Phosphor Bronze
- Contact Plating, Mating Area, Material = Gold (50)

Housing Features:

- Housing Entry Style = Side
- Housing Material = Polyester
- Housing Color = Black
- UL Flammability Rating = UL 94V-0

Configuration Features:

- Number of Conductors = 6

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Identification Marking:

- Keying = A

Other:

- Brand = AMP

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

