




EMI & EMC Solutions > IEC Inlets > Inlet Filters > FN9290 Power Entry Module with EMC Filter – Ultra-Compact Dual-Stage Filtering Solution



Filtering Requirements: **Filtered**

Current Rating (Max): **6 A**

Output Termination Type: **FASTON**

Pollution Degree: **PD2**

IP Rating: **IP40**

[All FN9290 Power Entry Module with EMC Filter – Ultra-Compact Dual-Stage Filtering Solution \(51\)](#)

Features

Product Type Features

Level Of Filtering	Inductor & Capacitor
Filter Switch Type	DPST
Filtering Requirements	Filtered
Output Termination Type	FASTON
Ground Choke Option	No

Configuration Features

Fuse Options	Dual
--------------	------

Electrical Characteristics

Capacitance Cy1	1.5
Capacitance Cy2	.47
Inductance L1	.78 μ H
Capacitance Cx1	220



Overvoltage Category	II
Current Rating (Max)	6 A
Leakage Current (Max) (120VAC, 60Hz)	280 µA
Leakage Current (Max) (250VAC, 50Hz)	160 µA

Body Features

Product Weight	153 g[5.39 oz]
----------------	----------------

Dimensions

Product Width	49.8 mm[1.96 in]
Product Length	32 mm[1.25 in]
Product Height	93 mm[3.66 in]

Operation/Application

Cooling Method	Natural Convection
----------------	--------------------

Industry Standards

Certified To	CSA 22.2 No. 8 1986, EN 60320, EN 60601-1, EN 60939, EN 60950, UL 1283, UL 544
Pollution Degree	PD2
IP Rating	IP40

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	未针对中国 RoHS 符合性进行审核 Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Also in the Series | Schaffner FN9290



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_814145-SF_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_814145-SF_G.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_814145-SF_G.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Power Entry Module with EMC Filter FN9290

English

Agency Approvals

CB SE-68739M1

English