

## 1-499786-0 Product Details

[Live Product Chat](#)



**1-499786-0**

TE Part Number: 1-499786-0

**Active**

[Add to Part List](#)

### Pin and Pinless Headers (AMP-LATCH)

[5 of 6 EU RoHS/ELV Compliant](#) ([Find RoHS Compliant Alternates/Statement of Compliance](#))

#### Product Highlights:

- Connector Type = Universal Ejection Pin Headers
- Standard Profile
- Number of Positions = 50
- 2.54 x 2.54 mm Centerline, Matrix
- PCB Mount Angle = Right Angle

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

**NEW!**

### Documentation & Additional Information

#### Product Drawings:

- [HEADER ASSY, UNIVERSAL, AMP-LATCH](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- [AMP-LATCH\\* and IDC Header Connectors, .100 x .100 In...](#) (PDF, English)

#### Application Specifications:

- None Available

#### Instruction Sheets:

- [AMP\\* INSTALLATION PROCEDURES FOR AMP-LATCH\\* UNIVERSA...](#) (PDF, English)

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version F)
- [3D Model](#) (IGES, Version F)
- [3D Model](#) (STEP, Version F)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Connector Type](#) = Universal Ejection Pin Headers
- [Profile](#) = Standard
- [Number of Positions](#) = 50
- [PCB Mount Angle](#) = Right Angle
- [PCB Retention Feature](#) = No
- [Mating Polarization Method](#) = Center, Dual Polarizing Bar, Military
- [Mating Connector Lock](#) = With
- [Housing Style](#) = 4-Sided
- [Ejection Latches](#) = With
- [Post Size \(mm \[in\]\)](#) = 0.64 [.025]
- [Shrouded](#) = Yes
- [PCB Thickness \(mm \[in\]\)](#) = 1.57 [0.062]
- [Mating Polarization](#) = With
- [Latch Type](#) = Long
- [Mating Connector Lock Type](#) = Latch

#### Termination Related Features:

- [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 2.79 [0.110]
- [Solder Tail Contact Plating](#) = Tin-Lead

#### Body Related Features:

- [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 x 2.54 [.100 x .100]

#### Contact Related Features:

- [Contact Mating Area Plating Material](#) = Gold (15)
- [Contact Shape](#) = Square

#### Housing Related Features:

- [Housing Material](#) = Thermoplastic
- [Housing Flammability Rating](#) = UL 94V-0
- [Housing Color](#) = Black

#### Industry Standards:

- [RoHS/ELV Compliance](#) = ELV compliant, 5 of 6 Compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

#### Conditions for Usage:

- [Temperature Rating](#) = Standard

#### Other:

- [Brand](#) = AMP