


## 1757829-1 Product Details

[Live Product Chat](#)



**1757829-1**

TE Part Number: 1757829-1

[Active](#)

[Add to Part List](#)

### Subminiature D Pin/Socket Connectors for MIL-C-24308 and MIL-C-39029

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Connector
- Product Series = 109
- Density = Standard
- Terminate To Printed Circuit Board
- Number of Positions = 9

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [PLUG ASSEMBLY,AMPLIMITE SERIES 109,SIZE 1 THRU 5 \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Additional Product Images:

- [Insert Arrangement](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Connector
- [Product Series](#) = 109
- [Number of Positions](#) = 9
- [Gender](#) = Plug
- [PCB Mount Angle](#) = Vertical
- [Shell Size](#) = 1
- [Shell Material](#) = Steel
- Mounting Hole Diameter (mm [in]) = 3.05 [.120]
- Comment = For solder dip product see part number 1757829-6.

#### Termination Related Features:

- [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 4.78 [0.188]

#### Body Related Features:

- [Blindmate](#) = No
- [Non-Magnetic](#) = No
- [Pins](#) = With
- [Rear Grommet](#) = No
- [Power/Signal/Coax Combination](#) = No
- [Shell Plating](#) = Zinc
- [Post Diameter \(mm \[in\]\)](#) = 0.76 [0.030]
- Mount Style = Mounting Holes
- Spacer Material = Aluminum Alloy
- Spacer Plating = Clear Blue Trichromate

#### Contact Related Features:

- [Contact Size](#) = 20
- Contact Material = Brass or Beryllium Copper
- Contact Mating Area Plating Material = Gold over Nickel

#### Configuration Related Features:

- [Density](#) = Standard

#### Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M24308/24-7
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- NASA Qualification = No

#### Conditions for Usage:

- Terminate To = Printed Circuit Board

#### Other:

- Brand = Tyco Electronics

[Provide Website Feedback](#) | [Need Help?](#)