


**1 - 826652 - 0 Product Details**

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**1 - 826652 - 0**

Active

**.100 inch AMPMODU Headers**

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

**Product Highlights:**

- ? Header
- ? Header Type = Breakaway
- ? Number of Rows = Single
- ? Number of Positions = 10
- ? Mating Post Length = 5.80 mm

[View all Features](#) | [Find Similar Products](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [AMPMODU II STIFTLISTE 90DEG EINREIHIG](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? None Available

**Application Specifications:**

- ? None Available

**Instruction Sheets:**

- ? None Available

**CAD Files:**

- ? None Available

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)

[List all Documents](#)

**Product Features**

(Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? [Product Type](#) = Header
- ? [Number of Positions](#) = 10
- ? [Mount Angle](#) = Right Angle
- ? [PCB Retention Feature](#) = No
- ? [Surface Mount Compatible](#) = No
- ? [Board Standoff](#) = Without
- ? [Mounting Ears](#) = Without
- ? [Mating Connector Lock](#) = Without
- ? Profile = Standard

**Mechanical Attachment:**

- ? [Mating Post Length \(mm \[in\]\)](#) = 5.80 [0.228]
- ? [Panel Attachment](#) = Without

**Termination Related Features:**

- ? [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 3.20 [0.126]
- ? Solder Tail Contact Plating = Tin

**Body Related Features:**

- ? [Header Type](#) = Breakaway
- ? [Number of Rows](#) = Single
- ? [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 [.100]
- ? [Selectively Loaded](#) = No
- ? [Mount Type](#) = PC Board

**Contact Related Features:**

- ? [Contact Mating Area Plating](#) = Gold (30)
- ? Contact Material = Phosphor Bronze

**Housing Related Features:**

- ? Housing Material = Thermoplastic Polyester
- ? Housing Flammability Rating = UL 94V -0

**Industry Standards:**

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

**Conditions for Usage:**

- ? [High Temperature Housing](#) = No

**Operation/Application:**

- ? [High Speed Serial Data Connector](#) = No

**Other:**

- ? Brand = AMP