


2057741-3 Product Details

[Share](#) | [Print](#) | [Email](#)


Impact High Density Backplane Connectors

IMP100,S,H,V2P16C,RG,39,5.5

2057741-3

TE Internal Number: 2057741-3

Active

[View 3D PDF](#)

Product Highlights [View All](#)

- Connector Style = Header
- 64/Signal, 32/Ground
- 96 Positions
- Header Type = Partially Shrouded
- Board-to-Board Configuration = Right Angle, Vertical

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

| Product Type Features | |
|--------------------------|------------------------------------|
| PCB Mount Retention Type | Action/Compliant Tail and Screw(s) |
| PCB Mount Alignment Type | Locating Post(s) |

| Electrical Characteristics | |
|-----------------------------|-------|
| Impedance (Ω) | 100 |
| Operating Voltage Reference | AC/DC |
| Operating Voltage (VAC) | 120 |
| Operating Voltage (VDC) | 120 |

| Dimensions | |
|-----------------------------------|----------------|
| Tail Length (mm [in]) | 1.2 [0.047] |
| Length (X-Axis) (mm [in]) | 36.90 [1.4528] |
| Width (Z-Axis) (mm [in]) | 12.70 [0.500] |
| Profile Height (Y-Axis) (mm [in]) | 11.95 [0.470] |
| PCB Hole Diameter (mm [in]) | 0.39 [0.015] |

| Body Features | |
|---------------|--------------------|
| Header Type | Partially Shrouded |

| Contact Features | |
|---|-----------------------|
| Contact Type | Pin |
| Contact Length (mm [in]) | 5.50 [0.217] |
| Contact Plating, Termination Area, Material | Matte Tin |
| Contact Plating, Termination Area, Thickness (μm [μin]) | 1.27 [50] |
| Contact Base Material | Copper-Nickel-Silicon |
| Underplate Material | Nickel |
| Underplate Material Thickness (μm [μin]) | 1.27 [50.000] |

| Housing Features | |
|-------------------|------------------------------|
| Connector Style | Header |
| End Wall Location | Open |
| Housing Color | Black |
| Housing Material | LCP (Liquid Crystal Polymer) |

| Configuration Features | |
|--|----------------------|
| Connector Contact Configuration (No. of Pos./Type) | 64/Signal, 32/Ground |
| Number of Positions | 96 |
| Number of Differential Pairs Per Column | 2 |
| Number of Columns | 16 |
| Number of Rows | 6 |
| Shrouded | Yes - Partial |
| Guide Location | Right |
| Tail Orientation | In-line |

| Industry Standards | |
|-----------------------------|------------------------------------|
| RoHS/ELV Compliance | RoHS compliant, ELV compliant |
| Lead Free Solder Processes | Not relevant for lead free process |
| RoHS/ELV Compliance History | Always was RoHS compliant |
| UL Rating | Recognized |
| UL File Number | E28476 |
| UL Flammability Rating | UL 94V-0 |
| CSA Certified | Yes |

| Environmental | |
|---------------------------------|------------------------|
| Operating Temperature (°C [°F]) | -55 - +85 [-67 - +185] |

| Conditions for Usage | |
|------------------------------|-----------------------|
| Board-to-Board Configuration | Right Angle, Vertical |

| Operation/Application | |
|-----------------------|-----------------------------|
| Industry Application | Networking (Communications) |

| Packaging Features | |
|--------------------|----------|
| Packaging Method | Tube/Box |

| Other | |
|-------|-----------------|
| Brand | TE Connectivity |

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

