


208063-2 Product Details

[Live Product Chat](#)



5mm (.197") Centerline, 600 V, 14 A max. (Metrimate)

[Not EU RoHS or ELV Compliant \(Find RoHS Compliant Alternates\)](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

208063-2

TE Part Number: 208063-2

[Active](#)

[Add to Part List](#)

Product Highlights:

- Housing
- Rectangular Connector Configuration
- Bus Configuration = Split
- Number of Positions = 36
- Receptacle

[View all Features](#) | [Find Similar Products](#)

Documentation & Additional Information

Product Drawings:

- [COMMONING DEVICE ASSEMBLY, 36 POSITION, METRIMATE](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Recommended Panel Cutout](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Housing
- [Number of Positions](#) = 36
- [Gender](#) = Receptacle
- [Keyed](#) = No
- [Mount](#) = Panel Mount
- [Mounting Ears](#) = Without
- [Mating Connector Lock](#) = With
- PCB Retention Feature = No
- Mating Polarization Method = Polarizing Tab
- Mating Connector Lock Type = Locking Tab
- Comment = Copper bus is divided lengthwise, providing dual 18-circuit busses.

Electrical Characteristics:

- Voltage (VAC) = 600

Termination Related Features:

- Solder Tail Contact Plating = Tin-Lead over Nickel

Body Related Features:

- [Connector Configuration](#) = Rectangular
- Bus Configuration = Split
- Coaxial Socket = Without
- [Centerline \(mm \[in\]\)](#) = 5.00 [0.197]
- [Jackscrew](#) = Without
- [8/32 Insert](#) = No
- Bus Material = Copper Alloy

Contact Related Features:

- Contact Mating Area Plating Material = Tin-Lead over Nickel

Housing Related Features:

- Housing Material = Thermoplastic
- Housing Color = Red
- Housing Flammability Rating = UL 94V-0

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

Packaging Related Features:

- Packaging Quantity = 200

Other:

- Brand = AMP