




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.03 mm²**

Mating Tab Width: **2.8 mm [.11 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------



Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	14.5 mm[.571 in]
Compatible Insulation Diameter Range	2.01 – 2.7 mm[.079 – .106 in]
Terminal Material Thickness	.25 mm[.01 in]
Wire Size	.51 – 1.03 mm²

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Quantity	15000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part




numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2150804-2 OCEAN-2.0-APPLICATOR-E-062F110F-REA	 TE Part # 2150804-1 OCEAN-2.0-APPLICATOR-E-062F110F-REM	 TE Part # 160534-1 110 FASTON,REC.,17-20 AWG,BR	 TE Part # 881608-1 110 FASTON REC 20-17 AWG BR
 TE Part # 881608-2 .110 S. FASTON REC.	 TE Part # 7-2150804-7 OCEAN_2.0_SPARE_PART_KIT-062F110F	 TE Part # 5-160555-2 110 FASTON REC 20-18 AWG TPBR	 TE Part # 1-160534-0 110 FASTON,REC.,17-20 AWG,BR
 TE Part # 444149-2 .110S FASTON REC	 TE Part # 160534-2 110 FASTON,REC.,17-20 AWG,TPBR	 TE Part # 160534-3 110 FASTON,REC.,17-20 AWG,BR	 TE Part # 626041-2 110 FASTON REC 22-16 AWG TPBR
 TE Part # 881607-1 110 FASTON REC 20-17 AWG BR			

Also in the Series | FASTON 110



Crimp Terminal Housings(13)



Insertion & Extraction Tools(1)




PCB Terminals(22)



Quick Disconnects(164)


Customers Also Bought



TE Part #41832
250 FASTON REC 18-14 AWG TPBR



TE Part #63520-1
PL 187 TERMINAL REC 20-16 AWG TPBR



TE Part #63608-2
187 FASTON REC 20-16 AWG TPBR



TE Part #141628-2
110 FASTON HSG.,REC.,1 POS, NATRUAL



TE Part #5-160430-7
187 FASTON REC 20-16 AWG TPBR



TE Part #925015
FF 110 REC HSG 3P NYLON NAT



TE Part #964267-2
TAB A 1.6x0.6 CONTACT CF SRC Sn



TE Part #2238027-4
250 FASTON,REC.,22-18 AWG,TPBR



TE Part #2383942-3
TERMI-BLOK SMD MOUNT 180_3P_3.5 MM



TE Part #60-0173-011-P00
CONTACT SOCKET 1,5 MM

Documents

Product Drawings

110 FASTON REC 20-17 AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_881607-2_F1_c-881607-2-f1.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_881607-2_F1_c-881607-2-f1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_881607-2_F1_c-881607-2-f1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English