


## 2-822064-4 Product Details

[Live Product Chat](#)



**2-822064-4**

TE Part Number: 2-822064-4

[Active](#)

[Add to Part List](#)

### PQFP Sockets

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Housing Sub-Assembly
- Number of Positions = 100
- .64 mm Centerline
- PQFP Type = Standard
- Package = Plastic

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [MICRO-PITCH SOCKET HOUSING SUB-ASSEMBLY REVERSE FOOT...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- [APPLICATION SPECIFICATION, MICRO PITCH, SOCKETS FOR ...](#) (PDF, English)

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Housing Sub-Assembly
- [Number of Positions](#) = 100
- [Package](#) = Plastic
- Color = Black
- Qty./Tube = 19
- Qty. Tubes/Box = 54
- Comment = Reverse footprint. .000200 tin over .000050 nickel. Max. height above PCB includes cover. Use with cover 821939-1.

#### Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 0.64 [0.025]
- PQFP Type = Standard

#### Contact Related Features:

- Contact Mount = Thru Hole
- Contact Material = Phosphor Bronze
- Contact Mating Area Plating Material = Tin over Nickel

#### Housing Related Features:

- Housing Material = High Temperature Thermoplastic
- Housing Flammability Rating = UL 94V-0

#### Configuration Related Features:

- [Height Above PC Board \(mm \[in\]\)](#) = 9.52 [0.375]

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

#### Packaging Related Features:

- Packaging Method = Tube

#### Other:

- Brand = AMP

[Provide Website Feedback](#) | [Need Help?](#)