




**+** CONNECTORS

RIBBON CABLE CONNECTORS



✓ Active

TE CONNECTIVITY (TE)

## A/L UNIV HDR 64P VERT SHT LAT BLUE

AMP-LATCH | Universal Headers

3-5499374-2

TE Internal Number: 3-5499374-2

EU RoHS Compliant

EU ELV Compliant

**Connector System** Wire-to-Board

**Number of Positions** 64

**Centerline (Pitch)** 2.54 mm [.1 in]

**PCB Mount Retention** Without

**PCB Mount Retention Type** Mounting Ears

[!\[\]\(1f56542a42e2413e44a2b2023033aa2e\_img.jpg\) \*\*PRODUCT DRAWING\*\*](#)  
English

[!\[\]\(19d44b37fb4fa155bf9d60c77a3d3cb2\_img.jpg\) \*\*3D PDF\*\*](#)

### DOCUMENTATION

Product Drawings

#### **HEADER ASSY, UNIVERSAL, AMP-LATCH**

PDF

**English**

CAD Files

#### **3D PDF**

PDF

**3D**

#### **Customer View Model**

2D\_DXF.ZIP

**English**

## Customer View Model

3D\_IGS.ZIP

English

## Customer View Model

3D\_STP.ZIP

English

---

Product Specifications

Product Specification

## AMP-LATCH And IDC Header Connectors, .100 X .100 Inch Grid

PDF

English

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

### Product Type Features

**Header Type** Universal Ejection Pin Headers

**Connector System** Wire-to-Board

**PCB Mounting Orientation** Vertical

**Shrouded** Yes

**Row-to-Row Spacing** 2.54 mm [ .1 in ]

**Connector Style** Plug

**Profile** Standard

**Connector & Contact Terminates To** Printed Circuit Board

**Connector Type** Header

**Board Standoff** Without

**Latch Type** Short

**Product Type** Connector

---

### Configuration Features

**Number of Positions** 64

**Number of Rows** 2

**Ejection Latches** With

---

### Electrical Characteristics

**Operating Voltage (VAC)** 250

**Insulation Resistance (MΩ)** 5000

---

### Body Features

**Post Size** .64 mm [ .025 in ]

---

### Contact Features

**Solder Tail Contact Plating Material** Tin  
**Contact Current Rating (Max) (A)** 1  
**Contact Mating Area Plating Material** Gold  
**Contact Type** Pin  
**Contact Termination Area Plating Thickness (µm)** 2.54  
**Contact Base Material** Brass, Phosphor Bronze  
**Contact Transmits (Typical)** Signal (Data)  
**Contact Termination Area Plating Material** Tin  
**Contact Mating Area Plating Thickness (µin)** 30

---

#### Termination Features

**Termination Method to PC Board** Through Hole  
**Termination Post Length** 3.94 mm [ .155 in ]

---

#### Mechanical Attachment

**Panel Mount Retention** Without  
**PCB Mount Alignment** Without  
**PCB Mount Retention** Without  
**PCB Mount Retention Type** Mounting Ears  
**Mating Alignment Type** Center, Dual Polarizing Bar  
**Mating Connector Lock** With  
**Mating Connector Lock Type** Latch  
**Mating Alignment** With  
**Mating Retention** With  
**Polarization** With

---

#### Housing Features

**Centerline (Pitch)** 2.54 mm [ .1 in ]  
**Housing Material** Glass Filled Nylon/Polyester  
**Housing Color** Blue  
**Housing Style** 4-Sided

---

#### Dimensions

**Shrouded End Dimension** 3.81 mm [ .15 in ]  
**PCB Thickness (Recommended)** 3.18 mm [ .125 in ]  
**Height** 13.94 mm [ .549 in ]  
**Length** 100.58 mm [ 3.959 in ]

---

#### Usage Conditions

**Operating Temperature Range (°C)** -65 – 105  
**Temperature Rating** Standard

---

#### Industry Standards

**UL Flammability Rating** UL 94V-0

---

#### Packaging Features

**Packaging Method** Box  
**Packaging Quantity** 24

---

Statement of Compliance

**Statement of Compliance**

PDF

---