


350217 -1 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



350217 -1

[Active](#)

.200" Centerline, 250 V, 13 A max.

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Contact
- ? Contact Diameter = 2.07 mm
- ? Strip
- ? Contact Type = Socket
- ? Wire Range = 0.50 -2.00² [20-14] mm [AWG]

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Housings \(70\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [SOCKET, MATE-N-LOK, DUAL LANCE](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? [MATE-N-LOK Dual Lance Pin And Socket Contacts](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)
- ? [Housings \(70\)](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Contact
- ? Wire Insulation Diameter (mm [in]) = 3.30 [0.130]
- ? Connector Line = Commercial MATE -N-LOK
- ? Comment = Dual Lance.

Electrical Characteristics:

- ? Voltage (VAC) = 250
- ? Current Rating (Amps.) = 13

Termination Related Features:

- ? Solder Tail Contact Plating = Pre -Tin

Body Related Features:

- ? Contact Diameter (mm [in]) = 2.07 [0.081]
- ? Wire Range (mm [AWG]) = 0.50 -2.00² [20-14]

Contact Related Features:

- ? Contact Type = Socket
- ? Contact Material = Brass

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? Packaging Method = Strip

Other:

- ? Brand = AMP