


4-1761184-1 Product Details

[Share](#) | [Print](#) | [Email](#)


4-1761184-1

SDL (Shielded Data Link)

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Cable Type = Flat
- Plug
- Product Series = 50 Series
- Receptacle Configuration = Standard

[View all Features](#)

TE Internal Number: 4-1761184-1

Active

[View 3D PDF](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [PLUG ASSY, FLAT CABLE, 50 SERIES, SDL \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [SDL Systemj Connector \(PDF, English\)](#)

Application Specifications:

- [36-Series and 50-Series Flat-Cable SDL Plug Connectors \(PDF, English\)](#)

Instruction Sheets:

- [SDL Plugs and Receptacles \(PDF, English\)](#)
- [Crimping Die Assemblies 58261-1, 58261-2, 58261-3, a... \(PDF, English\)](#)

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version A\)](#)
- [3D Model \(IGES, Version A\)](#)
- [3D Model \(STEP, Version A\)](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Cable Type = Flat
- Gender = Plug
- Product Series = 50 Series
- Receptacle Configuration = Standard
- Wire Size (mm² [AWG]) = 0.2² [24]
- PCB Mount Retention = Without
- Shield Material = Brass

Dimensions:

- Conductor Insulation Diameter (mm [in]) = 1.27 [0.050]

Body Features:

- Shield Plating = Tin over Nickel

Contact Features:

- Contact Base Material = Copper Alloy
- Contact Plating, Mating Area, Material = Gold (50)

Housing Features:

- Housing Material = Polycarbonate GF
- Housing Color = Smoke Gray

Configuration Features:

- Number of Conductors = 4

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Identification Marking:

- Keying = D

Other:

- Brand = AMP
- Comment = Prefix no. designates key configuration. Suffix no. is a code for the number of conductors. Prefix & suffix nos. of plug assemblies must match those of the intended mating receptacle. Keys are molded in as an integral part of the plug & receptacle.

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

