


494033 -3 Product Details


Live Product Chat US Only
 8:30am - 5pm ET, Mon - Fri

494033 -3
 [Active](#)

Flexible Film Contacts

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Pin
- ? Contact Type = Pin
- ? Wire Range = 0.20 -0.40² [24-22] mm [AWG]
- ? 2.54 mm Centerline
- ? Wire/Cable Type = Round Wire, Discrete

[View all Features](#) | [Find Similar Products](#)

Quick Links

[Check Pricing & Availability](#)
[Search for Tooling](#)
[View Housings \(149\)](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [CONTACT, PIN, .025 SQ ROUND WIRE, .100, FFC](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)
- ? [Housings \(149\)](#)

[List all Documents](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? Pin/Socket = Pin
- ? [Wire/Cable Type](#) = Round Wire, Discrete
- ? Wire Insulation Diameter (mm [in]) = 1.02 - 1.42 [0.040 - 0.056]
- ? Comment = Crimp Control Monitor 567561 -2 for AMP-O-LECTRIC.; Crimp Control Monitor 567561 -1 for AMPOMATOR CLS II Machine.; Use Extraction Tool No. 91092 -1 for end locking slot and Extraction Tool No. 91093 -1 for side locking lance slot.

Termination Related Features:

- ? Solder Tail Contact Plating = Matte Tin

Body Related Features:

- ? [Wire Range \(mm \[AWG\]\)](#) = 0.20 -0.40² [24-22]
- ? [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]

Contact Related Features:

- ? [Contact Type](#) = Pin
- ? [Contact Mating Area Plating Material](#) = Gold (15)
- ? Contact Underplating = Nickel (50)

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? [Packaging Method](#) = Strip

Other:

- ? Brand = AMP