


## 532533-1 Product Details

[Share](#) | 
 [Print](#) | 
 [Email](#)



532533-1

TE Internal Number: 532533-1

[Active](#)

### Eurocard Accessories

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Accessory Type = Shroud
- 96 Positions
- PCB Thickness, Recommended = 3.18 mm
- Used With Post Length 13.23 [.521]
- Size = Standard

[View all Features](#)

[Add to My Part List](#) | 
 [Request Sample](#) | 
 [Find Similar Products](#) | 
 [Buy Product](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [HEADER HOUSING EUROCARD](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Accessory Type](#) = Shroud
- [Size](#) = Standard
- [Mounting Holes](#) = With
- PCB Mount Retention = With
- [Used For](#) = Type C Connector, Type R Connector
- Color = Gray

#### Body Features:

- [Number of Positions](#) = 96
- [Used With](#) = Post Length 13.23 [.521]
- PCB Mount Retention Type = Mounting Ears
- Number of Rows = Triple

#### Housing Features:

- Housing Material = Valox 420 SEO
- UL Flammability Rating = UL 94V-0

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- [PCB Thickness, Recommended \(mm \[in\]\)](#) = 3.18 [0.125]

#### Other:

- Brand = Tyco Electronics
- Comment = Shrouds are for use with all 48 & 96 position, 3 row, Type C and R connectors mounted in 3.18 [.125], 2.36 [.093], and 1.57 [.062] thick PC boards. Twelve interference areas are located in selected cavities.

### Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

### Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

