



SMA Connectors for Flexible Cable (Continued)

Bulkhead Jacks, Crimp

Materials and Finishes

(See page 112)



Panel Thickness
.055-.103 [1.4-2.62]
**Recommended
Panel Cutout**



Connector Cable Range Selection Code [†]	RG/U Cable	Body and Coupling Nut Material and Plating	Style	M39012/ Military No. and/or Comments	Part No.	Dim. L	Integral Die Hand Tool	Die Insert for Pneumatic Tools 69365, 69365-3
B	174, 188, 188A, 316	Stainless Steel, Passivated	Mil Type	—	225608-4	1.060 26.93	220061-1	220091-1
		Brass, Nickel	Commercial	—	221169-2	1.188 30.18	220061-1	220091-1
D1	141, 141A, 303	Stainless Steel, Passivated	Mil Type	59B3024	225608-9	1.140 28.96	220061-1	220091-1
E1	142, 142A, 142B, 400, Belden 9246	Stainless Steel, Passivated	Mil Type	59B3022	225608-3	1.140 28.96	220061-1	220091-1
		Stainless Steel, Passivated	Mil Type	—	221169-1	1.188 30.18	220061-1	220091-1
—	188 Double Braid, 316 Double Braid	Stainless Steel, Passivated	Mil Type	—	1-225608-1	.950 24.13	59962-1	—
		Brass, Nickel	Commercial	—	221169-3	1.188 30.18	59962-1	—

[†]Refer to pages 14 and 15 for code specifications.

Panel Jacks, Crimp (4 Holes)

Materials and Finishes

(See page 112)




Maximum Panel Thickness .095 [2.41]
**Recommended
Panel Cutout**

Connector Cable Range Selection Code [†]	RG/U Cable	Body and Coupling Nut Material and Plating	Style	M39012/ Military No. and/or Comments	Part No.	Dim. L	Integral Die Hand Tool	Die Insert for Pneumatic Tools 69365, 69365-3
B	174, 188, 188A, 316	Brass, Nickel	Commercial	—	221126-2	1.188 30.18	220061-1	220091-1
E1	142, 142A, 142B, 400, Belden 9246	Brass, Nickel	Commercial	—	221126-1	1.188 30.18	220061-1	220091-1
—	188 Double Braid, 316 Double Braid	Brass, Nickel	Commercial	—	221126-3	1.188 30.18	59962-1	—

[†]Refer to pages 14 and 15 for code specifications.

Panel Jacks, Crimp (2 Holes)

Maximum Panel Thickness .095 [2.41]
**Recommended
Panel Cutout**



Connector Cable Range Selection Code [†]	RG/U Cable	Body and Coupling Nut Material and Plating	Style	M39012/ Military No. and/or Comments	Part No.	Dim. L	Integral Die Hand Tool	Die Insert for Pneumatic Tools 69365, 69365-3
E1	142	Stainless Steel, Passivated	Commercial	—	448834-1	1.188 30.18	220051-1	220091-1
B	316, 188, 174	Stainless Steel, Passivated	Commercial	—	448834-2	1.188 30.18	220051-1	220091-1
—	316, 188 Double Braid	Stainless Steel, Passivated	Commercial	—	448834-3	1.188 30.18	59962-1	—