


## FSK-21.5A-8 Product Details

[Live Product Chat](#)



### FSK-21.5A-8

TE Part Number: 9-1437209-6

**Active**

[Add to Part List](#)

### FLEXSTRIP® Jumpers

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

#### Product Highlights:

- 2.54 mm Centerline
- Kapton Insulation Material
- Insulation Length = 38.10 mm
- Pin Arrangement (Left) = A
- Pin Arrangement (Right) = A

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

**NEW!**

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Additional Product Images:

- [Product View](#)
- [Product View](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Insulation Material](#) = Kapton
- [Number of Conductors](#) = 8

#### Electrical Characteristics:

- Current Rating (Amps.) = 3
- Impedance (Ω) = 117
- Voltage Rating (VAC) = 300

#### Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- [Insulation Length \(mm \[in\]\)](#) = 38.10 [1.500]

#### Configuration Related Features:

- [Pin Arrangement \(Left\)](#) = A
- [Pin Arrangement \(Right\)](#) = A

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- Operating Temperature (°C [°F]) = -40 - +150 [-40 - +302]

#### Other:

- Brand = Tyco Electronics