

## 2-1393531 -9 Product Details

### Have a Question?

Chat with a Product Information Specialist



**2-1393531 -9**

TE Internal Number: 2 -1393531 -9

[Active](#)

### Ribbon Cable Connectors (AMP - LATCH)

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Preloaded
- ? Connector Type = AMP - LATCH, BK -MOD 422
- ? Housing Gender = Receptacle
- ? 16 Positions
- ? Receptacle

[View all Features](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) | 
 [Request Sample](#) | 
 [Find Similar Products](#) | 
 [Buy Product](#)

#### Documentation & Additional Information

##### Product Drawings:

- ? [Customer Drawing \(1\)](#) (PDF, English)
- ? [Customer Drawing \(2\)](#) (PDF, English)

##### Catalog Pages/Data Sheets:

- ? None Available

##### Product Specifications:

- ? None Available

##### Application Specifications:

- ? None Available

##### Instruction Sheets:

- ? None Available

##### CAD Files:

- ? None Available

##### Additional Information:

- ? [Product Line Information](#)

##### Related Products:

- ? [Tooling](#)

[List all Documents](#)

#### Product Features (Please use the Product Drawing for all design activity)

##### Product Type Features:

- ? Connector Type = AMP - LATCH, BK -MOD 422
- ? Gender = Receptacle
- ? Mating Polarization Type = Center & Military
- ? [Mating Polarization](#) = With
- ? Wire/Cable Type = Ribbon Cable
- ? [Mounting Ears](#) = Without
- ? PCB Mount Retention = Without
- ? Mating Connector Lock = Without
- ? Strain Relief = Without
- ? With Cover Preassembled = Yes

##### Termination Related Features:

- ? [Solder Tail Contact Plating](#) = Tin

##### Body Related Features:

- ? [Number of Positions](#) = 16
- ? Centerline, Matrix (mm [in]) = 2.54 x 2.54 [.100 x .100]

##### Contact Related Features:

- ? Preloaded = Yes
- ? [Contact Plating, Mating Area, Material](#) = Gold (15) over Palladium Nickel
- ? Contact Base Material = Copper -Nickel -Tin
- ? Approved Standards = IEC 603 -13

##### Housing Related Features:

- ? Housing Gender = Receptacle
- ? [Housing Color](#) = Gray
- ? Housing Material = PBTP GF
- ? Housing Flammability Rating = UL 94V -0

##### Configuration Related Features:

- ? Cable Stop = Without

##### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

##### Conditions for Usage:

- ? [Applies To](#) = Cable

##### Other:

- ? Brand = AMP

#### Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

#### Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

#### Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

#### Sign up for our eNewsletter

Enter your email address

Follow us on:

