


5520242-2 Product Details

Share | Print | Email



5520242-2

TE Internal Number: 5520242-2

Active

View 3D PDF

PCB Mounted Jacks - Single Port, Multi-port and Stacked

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Preloaded
- Single Port Configuration
- 1 x 1 Jack Configuration
- Jack Type = RJ14

View all Features

Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Documentation & Additional Information

<p>Product Drawings:</p> <ul style="list-style-type: none"> • PRINTED CIRCUIT BOARD MODULAR JACK ASSEMBLY SIDE ENT... (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • Modular Plugs, Thru-Hole and Surface Mount Jacks, Da... (PDF, English) <p>Application Specifications:</p> <ul style="list-style-type: none"> • Modular Jacks (PDF, English) <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> • 2D Drawing (DXF, Version A) • 3D Model (IGES, Version A) • 3D Model (STEP, Version A) 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling
---	--

List all Documents

Product Features (Please use the Product Drawing for all design activity)

<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Connector • Jack Type = RJ14 • PCB Mounting Orientation = Side Entry (Right Angle) • PCB Mount Style = Through Hole • Termination Method to PC Board = Solder • Performance Category = Cat 3 • LED = Without • Grounding Options = Without • Panel Stops = Without • Keyed = No • Profile = Standard • Color = Black • Latch Style = Standard • PCB Mount Retention Type = 3 Quarter/PAC-Man Style Posts <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> • Panel Mount Retention = With • Flanged = Yes <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Shielded = No <p>Termination Features:</p> <ul style="list-style-type: none"> • Solder Tail Contact Plating = Tin over Nickel <p>Dimensions:</p> <ul style="list-style-type: none"> • Height (mm [in]) = 17.40 [0.685] • PCB Tail Length (mm [in]) = 3.44 [0.135] • PCB Thickness, Recommended (mm [in]) = 1.57 [0.062] 	<p>Body Features:</p> <ul style="list-style-type: none"> • Inverted Jack Face = No <p>Contact Features:</p> <ul style="list-style-type: none"> • Contact Plating, Mating Area, Material = Gold (50) • Contact Base Material = Phosphor Bronze <p>Housing Features:</p> <ul style="list-style-type: none"> • Housing Material = PBT - GF • UL Flammability Rating = UL 94V-0 <p>Configuration Features:</p> <ul style="list-style-type: none"> • Preloaded = Yes • Port Configuration = Single • Jack Configuration = 1 x 1 • Number of Positions = 6 • Number of Contacts Loaded = 4 <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C • RoHS/ELV Compliance History = Always was RoHS compliant <p>Packaging Features:</p> <ul style="list-style-type: none"> • Packaging Method = Tray <p>Product Availability:</p> <ul style="list-style-type: none"> • Region = Asia, North America <p>Other:</p> <ul style="list-style-type: none"> • Brand = AMP
--	--

Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy

Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

Keep Me Informed

