


5536255-1 Product Details

[Share](#) | [Print](#) | [Email](#)


5536255-1

TE Internal Number: 5536255-1
✔ Active

[View 3D PDF](#)

.050 Centerline Micro-Strip Connectors

✔ Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Connector Style = Receptacle
- 40 Positions
- Vertical Mount Angle
- Termination Method to PC Board = Through Hole - Solder

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [RECEPTACLE ASSEMBLY, VERTICAL, 4.57\[.180\] TAIL, BOAR...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Micro-Strip board to Board Connector](#) (PDF, English)

Application Specifications:

- [Micro-Strip Board-To-Board Plug and Receptacle Conne...](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version 01\)](#)
- [3D Model \(IGES, Version 01\)](#)
- [3D Model \(STEP, Version 01\)](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Mount Angle](#) = Vertical
- [Termination Method to PC Board](#) = Through Hole - Solder
- [PCB Mount Retention](#) = Without
- [Guides](#) = Without
- [Flame Retardant](#) = Yes

Termination Features:

- [Tail Length \(mm \[in\]\)](#) = 4.5 [0.177]

Body Features:

- [Bus Bar Material](#) = Phosphor Bronze
- [Bus Bar Mating Area Plating](#) = Gold (30)
- [Bus Bar Termination Area Plating](#) = Matte Tin with Nickel underplated

Contact Features:

- [Signal Contact Material](#) = Phosphor Bronze
- [Signal Contact Mating Area Plating](#) = Gold (30)
- [Signal Contact Termination Area Plating](#) = Matte Tin with Nickel underplated

Housing Features:

- [Connector Style](#) = Receptacle
- [Housing Material](#) = High Temperature Thermoplastic

Configuration Features:

- [Number of Positions](#) = 40
- [Stack Height \(mm \[in\]\)](#) = 10.92 [0.430], 18.75 [0.738]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Other:

- [Brand](#) = AMP

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address [▶](#)

