


3 - 1393531 - 4 Product Details

Have a Question?

Chat with a Product Information Specialist



3 - 1393531 - 4

TE Internal Number: 3 - 1393531 - 4

[Active](#)

Ribbon Cable Connectors (AMP - LATCH)

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Preloaded
- ? Connector Type = AMP - LATCH, BK - MOD 422
- ? Housing Gender = Receptacle
- ? 34 Positions
- ? Receptacle

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- ? [Customer Drawing \(1\)](#) (PDF, English)
- ? [Customer Drawing \(2\)](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Connector Type = AMP - LATCH, BK - MOD 422
- ? Gender = Receptacle
- ? Mating Polarization Type = Center & Military
- ? [Mating Polarization](#) = With
- ? Wire/Cable Type = Ribbon Cable
- ? [Mounting Ears](#) = Without
- ? PCB Mount Retention = Without
- ? Mating Connector Lock = Without
- ? Strain Relief = Without
- ? With Cover Preassembled = Yes

Termination Related Features:

- ? [Solder Tail Contact Plating](#) = Tin

Body Related Features:

- ? [Number of Positions](#) = 34
- ? Centerline, Matrix (mm [in]) = 2.54 x 2.54 [.100 x .100]

Contact Related Features:

- ? Preloaded = Yes
- ? [Contact Plating, Mating Area, Material](#) = Gold (15) over Palladium Nickel
- ? Contact Base Material = Copper - Nickel - Tin
- ? Approved Standards = IEC 603 - 13

Housing Related Features:

- ? Housing Gender = Receptacle
- ? [Housing Color](#) = Gray
- ? Housing Material = PBTP GF
- ? Housing Flammability Rating = UL 94V - 0

Configuration Related Features:

- ? Cable Stop = Without

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Applies To](#) = Cable

Other:

- ? Brand = AMP

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow us on:

