


1757825-3 Product Details



1757825-3
(M24308/4-331)

TE Internal Number: 1757825-3

 Active

Subminiature D Pins/Sockets for MIL-C-24308 and MIL-C-39029

 Always EU RoHS/ELV Compliant (Statement of Compliance)


Product Highlights:

- Connector
- Product Series = 90
- Connector Style = Plug
- Accepts Contact Gender = Pin
- Density = High

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Insert Arrangement](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Product Series](#) = 90
- [Shell Size](#) = 3
- [Shell Material](#) = Steel
- [Termination Method to Wire/Cable](#) = Crimp
- Mounting Hole Diameter (mm [in]) = 3.05 [.120]
- Comment = "F" is stamped on connectors following M24308 part number as required. "F" designates cadmium shell plating.; Supplied without sockets.

Body Related Features:

- [Number of Positions](#) = 44
- [Blindmate](#) = No
- [Non-Magnetic](#) = No
- [Rear Grommet](#) = No
- [Power/Signal/Coax Combination](#) = No
- [Shell Plating](#) = Zinc
- Mount Style = Dual Floating Bushing
- Retention Clip Material = Stainless Steel

Contact Related Features:

- Accepts Contact Gender = Pin
- [Contact Size](#) = 22
- [Contact Style](#) = Crimp Snap-in

Housing Related Features:

- Connector Style = Plug

Configuration Related Features:

- [Density](#) = High

Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M24308/4-331
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- NASA Qualification = No

Conditions for Usage:

- Applies To = Wire

Other:

- Brand = AMP

 BOOKMARK   

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

