


647284 -3 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



647284 -3

✓ [Active](#)

MTA, CST -100 II, MT -6 and SL Connectors and Headers

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? CST-100 Housings
- ? Number of Positions = 3
- ? Mating Type = Receptacle
- ? Wire -to -Board Application
- ? 2.54 mm Contact Centerline Spacing

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [HOUSING,SPECIAL,CST -100](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Additional Product Images:

- ? [Product Photo](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = CST -100 Housings
- ? [Number of Positions](#) = 3
- ? [Mating Type](#) = Receptacle
- ? [Wire Termination Type](#) = Crimp
- ? [Mating Polarization](#) = Without
- ? [Mating Connector Lock](#) = With
- ? [Four Points of Contact](#) = Without
- ? [Shrouded](#) = No
- ? [Mounting Ears](#) = Without
- ? Comment = Accepts Contact Part No. 770601 - 1.

Mechanical Attachment:

- ? [Panel Attachment](#) = Without

Body Related Features:

- ? Cable Exit Angle = 180°

Contact Related Features:

- ? [Contact Centerline Spacing \(mm \[in\]\)](#) = 2.54 [0.100]

Housing Related Features:

- ? Housing Color = Natural
- ? Housing Flammability Rating = UL 94V -0
- ? Housing Material = Nylon

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- ? [Application](#) = Wire -to -Board

Other:

- ? Brand = AMP