


7-530654 -6 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



7-530654 -6

[Active](#)

.125, .156 Centerline Low Profile Connectors

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? 22 Dual Positions
- ? 3.96 mm Centerline
- ? Row-to -Row Spacing = 5.97 mm
- ? Post Type = Solder Eyelet Contact
- ? With Mounting Ears

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? None Available

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [Connector, Edge, Low Profile](#) (PDF, English)

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Additional Product Images:

- ? [PCB Layout](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Number of Dual Positions](#) = 22
- ? [Post Type](#) = Solder Eyelet Contact
- ? [Mounting Ears](#) = With
- ? [Mounting Ear Style](#) = Without Threaded Inserts
- ? Comment = Intercontact Keying Plug Part Number 650025 -2.

Termination Related Features:

- ? [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 7.11 [0.280]

Body Related Features:

- ? [Centerline \(mm \[in\]\)](#) = 3.96 [0.156]
- ? [Row-to -Row Spacing \(mm \[in\]\)](#) = 5.97 [0.235]
- ? Post Plating = Bright Tin (100)

Contact Related Features:

- ? Contact Material = Phosphor Bronze
- ? Contact Mating Area Plating Material = Gold (30)
- ? Contact Underplating = Nickel (30)

Housing Related Features:

- ? Housing Material = Polyester GF
- ? Housing Color = Green

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- ? Brand = Tyco Electronics