




[CONNECTORS](#)

[RF CONNECTORS](#)



✓ Active

TE CONNECTIVITY (TE)

2058 5328 02

Subminiature Coax | SM , SMA

1053261-1

TE Internal Number: 1053261-1

Alias ID: 2058-5328-02

[EU RoHS Compliant with Exemptions](#)

[EU ELV Compliant with Exemptions](#)

**Connector Interface** SMA

**Connector Style** Jack

**Mated Outer Diameter (Approximate)** 6.35 mm [ .25 in ]

**Impedance (Ω)** 50

**Operating Frequency (GHz)** 18

[↓ PRODUCT DRAWING](#)  
English

[↓ 3D PDF](#)

## DOCUMENTATION

Product Drawings

### OSM PANEL FEEDTHROUGH JACK RECEPTACLE

PDF (TIFF AVAILABLE)

English

CAD Files

### 3D PDF

PDF

3D

### Customer View Model

2D\_DXF.ZIP

English

## Customer View Model

3D\_IGS.ZIP

English

## Customer View Model

3D\_STP.ZIP

English

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

### Product Type Features

**Connector Interface** SMA

**Connector Style** Jack

---

### Electrical Characteristics

**Impedance ( $\Omega$ )** 50

---

### Body Features

**Cable Connector Orientation** Straight

**Body Material** Stainless Steel

**Body Finish** Passivated

---

### Contact Features

**Center Contact Plating Material** Gold over Copper

**Center Contact Material** Beryllium Copper

**Connector Product Type** Connector Assembly

**RF Connector Contact Configuration** Captivated Contacts

---

### Mechanical Attachment

**Connector Mounting Type** Panel

**Panel Attachment Style** Front Mount, Rear Mount

---

### Dimensions

**Mated Outer Diameter (Approximate)** 6.35 mm [ .25 in ]

**Pin Diameter Accepted** .51 mm [ .02 in ]

**Length** 10.8 mm [ .425 in ]

---

### Operation/Application

**Operating Frequency (GHz)** 18

---

### Packaging Features

**Packaging Method** Bag

---

Other

**Dielectric Material** TFE Fluorocarbon

**Comment** Accepts 0.5mm [.020] dia. pin

---

## PRODUCT COMPLIANCE



Statement of Compliance

**Statement of Compliance**

PDF

---