


1060442-1 Product Details

[Live Product Chat](#)



1060442-1

TE Part Number: 1060442-1

[Active](#)

[Add to Part List](#)

SMB RF Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- Jack
- Standard
- Terminate To Coaxial Cable
- Coupler Style = Quick Connect/Disconnect

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Gender](#) = Jack
- Connector Series = Standard
- [Body Style](#) = Straight
- [Grade](#) = Commercial
- Panel Thickness (mm [in]) = 2.36 [0.093]
- Dielectric Material = TFE Fluorocarbon
- Solder Pot = With

Mechanical Attachment:

- [Panel Attachment](#) = With
- [Panel Attachment Style](#) = Front Mount
- Panel Attachment Method = Bulkhead

Electrical Characteristics:

- [Connector Impedance \(Ω\)](#) = 50
- Environmental Seal = Without

Body Related Features:

- Coupler Style = Quick Connect/Disconnect
- [Pin Protection](#) = Without
- Solder Lug = Without
- [Body Plating](#) = Gold per MIL-G-45204, Type II, Grade C, Class 1
- Terminal Style = Solder Pot

Contact Related Features:

- [Center Contact Plating](#) = Gold over Copper
- Contacts = With

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Terminate To](#) = Coaxial Cable

Other:

- Brand = AMP