
826629-4 Product Details

Live Product Chat



826629-4

TE Part Number: 826629-4
Active
Add to Part List

.100 inch AMPMODU Headers

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:
- Header
- Header Type = Breakaway
- Number of Rows = Single
- Number of Positions = 4
- Mating Post Length = 6.70 mm

View all Features | Find Similar Products

Quick Links
- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product
- Request Samples NEW!

Documentation & Additional Information

Product Drawings:
- AMPMODU II STIFTLEISTEN, EINREIHIG (PDF, German)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files: (CAD Format & Compression Information)
- 2D Drawing (DXF, Version Y2)
- 3D Model (IGES, Version Y2)
- 3D Model (STEP, Version Y2)

List all Documents

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Product Type = Header
- Number of Positions = 4
- Mount Angle = Vertical
- PCB Retention Feature = No
- Surface Mount Compatible = No
- Board Standoff = Without
- Mounting Ears = Without
- Mating Connector Lock = Without
- Profile = Standard

Mechanical Attachment:
- Mating Post Length (mm [in]) = 6.70 [0.264]
- Panel Attachment = Without

Termination Related Features:
- Termination (Solder) Post Length (mm [in]) = 3.20 [0.126]
- Solder Tail Contact Plating = Tin

Body Related Features:
- Header Type = Breakaway
- Number of Rows = Single
- Centerline, Matrix (mm [in]) = 2.54 [.100]
- Selectively Loaded = No
- Mount Type = PC Board

Contact Related Features:
- Contact Mating Area Plating Material = Gold (30)
- Contact Material = Phosphor Bronze

Housing Related Features:
- Housing Material = Thermoplastic Polyester
- Housing Flammability Rating = UL 94V-0

Industry Standards:
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260° C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:
- High Temperature Housing = No

Operation/Application:
- High Speed Serial Data Connector = No

Packaging Related Features:
- Packaging Quantity = 1,500

Other:
- Brand = AMP

© 2008 Tyco Electronics Corporation All Rights Reserved