


 [Live Product Chat](#)



✓ Active

 Add to Part List

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Connector
- Jack
- Standard
- Terminate To Printed Circuit Board
- Coupler Style = Quick Connect/Disconnect

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

- [SMB RIGHT ANGLE PRINTED CIRCUIT BOARD JACK RECEPTACLE... \(PDF, English\)](#)

- None Available

- None Available

- None Available

- None Available

- None Available

- Product Line Information

- Tooling

List all Documents

- [Product Type](#) = Connector
- [Gender](#) = Jack
- Connector Series = Standard
- [Body Style](#) = Right Angle
- [Grade](#) = Commercial
- [PCB Mount Angle](#) = Right Angle
- [Board Standoff](#) = With
- PCB Mount Style = Thru Hole
- Body Material = Brass
- Profile = Standard
- Dielectric Material = TFE Fluorocarbon
- Comment = Captured Center Contact

- Panel Attachment = With
- Panel Attachment Style = Rear Mount

- Connector Impedance (Ω) = 50
- Environmental Seal = Without

- PCB Leg Plating = Gold

- Coupler Style = Quick Connect/Disconnect
- [Pin Protection](#) = Without
- Solder Lug = Without
- [Body Plating](#) = Gold
- Overall Length (mm [in]) = 11.00 [0.432]
- Terminal Style = Straight Pin

- Center Contact Plating = Gold
- Contacts = With
- Center Contact Material = Brass

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

- Terminate To = Printed Circuit Board

- Brand = AMP