




CONNECTORS

MULTIPLE CONFIGURATION PCB HEADERS & RECEPTACLES



✓ Active

TE CONNECTIVITY (TE)

6P AMPMODU II STIFT LEI

AMPMODU | AMPMODU Headers

826648-6

TE Internal Number: 826648-6

EU RoHS Compliant

EU ELV Compliant

Number of Positions 6

Centerline (Pitch) 2.54 mm [.1 in]

Connector & Contact Terminates To Printed Circuit Board

Connector Style Plug

Header Type Breakaway

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

AMPMODU II STIFTLISTEN 90 DEG. ,EINREIHIG

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Environmental Compliance

TE Material Declaration

MD_826648-6_12092015836_dmtec

PDF

English

Agency Approvals

Agency Approval Document

AMPMODU CONNECTOR REPORT (GERMANY)

PDF

English

UL Report

AMPMODU CONNECTOR REPORT

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector & Contact Terminates To Printed Circuit Board

Connector Style Plug

Header Type Breakaway

PCB Mounting Orientation Vertical

Connector Type Header

Row-to-Row Spacing 2.54 mm [.1 in]

Gasket Without

Profile Standard

Product Type Connector

Stabilizers Without

Board Standoff Without

Strain Relief Without

Configuration Features

Selectively Loaded No

Number of Positions 6

Number of Rows 1

Keyed No

Body Features

Post Size .63 mm [.024 in]

Contact Features

Solder Tail Contact Plating Material Tin
Contact Protection Without
Contact Shape Square
Contact Base Material Phosphor Bronze
Contact Mating Area Plating Thickness (µm) .8
Contact Type Pin
Contact Mating Area Plating Material Gold

Termination Features

Termination Method to PC Board Through Hole
Termination Post Length 3.2 mm [.1259 in]
Termination End Plating Material Tin over Nickel
Termination End Plating Thickness (µm) 3

Mechanical Attachment

Panel Mount Retention Without
Mating Connector Lock Without
PCB Mounting Style Straddle Mount
PCB Mount Retention Without
Mating Alignment Without

Housing Features

Centerline (Pitch) 2.54 mm [.1 in]
Housing Material PBT GV
Housing Color Green

Dimensions

Mating Post Length 8 mm [.315 in]

Usage Conditions

High Temperature Housing No

Operation/Application

High Speed Serial Data Connector No

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Quantity 1500
Packaging Method Box

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
