


829492-4 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



829492-4

Active

.100 inch AMPMODU Headers

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Header
- Header Type = Breakaway
- Number of Rows = Triple
- Number of Positions = 12
- Mating Post Length = 7.00 mm

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [AMPMODU II PINHEADER TRIPLE ROW STIFTLISTE DREIREIHIG](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Header
- [Number of Positions](#) = 12
- [Mount Angle](#) = Vertical
- [PCB Retention Feature](#) = No
- [Surface Mount Compatible](#) = No
- [Board Standoff](#) = Without
- [Mounting Ears](#) = Without
- [Mating Connector Lock](#) = Without
- Profile = Standard
- Comment = Headers are side-to-side stackable.

Mechanical Attachment:

- [Mating Post Length \(mm \[in\]\)](#) = 7.00 [0.276]
- [Panel Attachment](#) = Without

Termination Related Features:

- [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 3.15 [0.124]
- Solder Tail Contact Plating = Tin

Body Related Features:

- [Header Type](#) = Breakaway
- [Number of Rows](#) = Triple
- [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 x 2.54 x 2.54 [.100 x .100 x .100]
- [Selectively Loaded](#) = No
- [Mount Type](#) = PC Board

Contact Related Features:

- [Contact Mating Area Plating](#) = Gold (30)
- Contact Material = Phosphor Bronze

Housing Related Features:

- Housing Material = Thermoplastic Polyester
- Housing Flammability Rating = UL 94V-0

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [High Temperature Housing](#) = No

Operation/Application:

- [High Speed Serial Data Connector](#) = No

Other:

- Brand = AMP